

# Center Distance Factor Tables

TECHNICAL SECTION

Table 42 (Cont.)

| N1 - N2 | NB - N1 |         |         |         |         |         |         |         |         |         |         |         |
|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
|         | 265     | 266     | 267     | 268     | 269     | 270     | 271     | 272     | 273     | 274     | 275     | 276     |
| 1       | 132.750 | 133.250 | 133.750 | 134.250 | 134.750 | 135.250 | 135.750 | 136.250 | 136.750 | 137.250 | 137.750 | 138.250 |
| 2       | 133.000 | 133.500 | 134.000 | 134.500 | 135.000 | 135.500 | 136.000 | 136.500 | 137.000 | 137.500 | 138.000 | 138.500 |
| 3       | 133.249 | 133.749 | 134.249 | 134.749 | 135.249 | 135.749 | 136.249 | 136.749 | 137.249 | 137.749 | 138.249 | 138.749 |
| 4       | 133.498 | 133.998 | 134.498 | 134.998 | 135.499 | 135.999 | 136.499 | 136.999 | 137.499 | 137.999 | 138.499 | 138.999 |
| 5       | 133.748 | 134.248 | 134.748 | 135.248 | 135.748 | 136.248 | 136.748 | 137.248 | 137.748 | 138.248 | 138.748 | 139.248 |
| 6       | 133.997 | 134.497 | 134.997 | 135.497 | 135.997 | 136.497 | 136.997 | 137.497 | 137.997 | 138.497 | 138.997 | 139.497 |
| 7       | 134.245 | 134.745 | 135.245 | 135.745 | 136.245 | 136.745 | 137.245 | 137.745 | 138.246 | 138.746 | 139.246 | 139.746 |
| 8       | 134.494 | 134.994 | 135.494 | 135.994 | 136.494 | 136.994 | 137.494 | 137.994 | 138.494 | 138.994 | 139.494 | 139.994 |
| 9       | 134.742 | 135.242 | 135.742 | 136.242 | 136.742 | 137.243 | 137.743 | 138.243 | 138.743 | 139.243 | 139.743 | 140.243 |
| 10      | 134.991 | 135.491 | 135.991 | 136.491 | 136.991 | 137.491 | 137.991 | 138.491 | 138.991 | 139.491 | 139.991 | 140.491 |
| 11      | 135.239 | 135.739 | 136.239 | 136.739 | 137.239 | 137.739 | 138.239 | 138.739 | 139.239 | 139.739 | 140.239 | 140.739 |
| 12      | 135.487 | 135.987 | 136.487 | 136.987 | 137.487 | 137.987 | 138.487 | 138.987 | 139.487 | 139.987 | 140.487 | 140.987 |
| 13      | 135.734 | 136.234 | 136.734 | 137.234 | 137.734 | 138.235 | 138.735 | 139.235 | 139.735 | 140.235 | 140.735 | 141.235 |
| 14      | 135.982 | 136.482 | 136.982 | 137.482 | 137.982 | 138.482 | 138.982 | 139.482 | 139.982 | 140.482 | 140.982 | 141.482 |
| 15      | 136.229 | 136.729 | 137.229 | 137.729 | 138.229 | 138.729 | 139.230 | 139.730 | 140.230 | 140.730 | 141.230 | 141.730 |
| 16      | 136.476 | 136.976 | 137.476 | 137.977 | 138.477 | 138.977 | 139.477 | 139.977 | 140.477 | 140.977 | 141.477 | 141.977 |
| 17      | 136.723 | 137.223 | 137.723 | 138.224 | 138.724 | 139.224 | 139.724 | 140.224 | 140.724 | 141.224 | 141.724 | 142.224 |
| 18      | 136.970 | 137.470 | 137.970 | 138.470 | 138.970 | 139.471 | 139.971 | 140.471 | 140.971 | 141.471 | 141.971 | 142.471 |
| 19      | 137.217 | 137.717 | 138.217 | 138.717 | 139.217 | 139.717 | 140.217 | 140.718 | 141.218 | 141.718 | 142.218 | 142.718 |
| 20      | 137.463 | 137.963 | 138.463 | 138.964 | 139.464 | 139.964 | 140.464 | 140.964 | 141.464 | 141.964 | 142.464 | 142.965 |
| 21      | 137.709 | 138.210 | 138.710 | 139.210 | 139.710 | 140.210 | 140.710 | 141.210 | 141.711 | 142.211 | 142.711 | 143.211 |
| 22      | 137.956 | 138.456 | 138.956 | 139.456 | 139.956 | 140.456 | 140.957 | 141.457 | 141.957 | 142.457 | 142.957 | 143.457 |
| 23      | 138.202 | 138.702 | 139.202 | 139.702 | 140.202 | 140.702 | 141.203 | 141.703 | 142.203 | 142.703 | 143.203 | 143.703 |
| 24      | 138.447 | 138.947 | 139.448 | 139.948 | 140.448 | 140.948 | 141.448 | 141.949 | 142.449 | 142.949 | 143.449 | 143.949 |
| 25      | 138.693 | 139.193 | 139.693 | 140.194 | 140.694 | 141.194 | 141.694 | 142.194 | 142.695 | 143.195 | 143.695 | 144.195 |
| 26      | 138.938 | 139.439 | 139.939 | 140.439 | 140.939 | 141.439 | 141.940 | 142.440 | 142.940 | 143.440 | 143.941 | 144.441 |
| 27      | 139.184 | 139.684 | 140.184 | 140.684 | 141.185 | 141.685 | 142.185 | 142.685 | 143.186 | 143.686 | 144.186 | 144.686 |
| 28      | 139.429 | 139.929 | 140.429 | 140.930 | 141.430 | 141.930 | 142.430 | 142.931 | 143.431 | 143.931 | 144.431 | 144.931 |
| 29      | 139.674 | 140.174 | 140.674 | 141.175 | 141.675 | 142.175 | 142.675 | 143.176 | 143.676 | 144.176 | 144.676 | 145.177 |
| 30      | 139.919 | 140.419 | 140.919 | 141.419 | 141.920 | 142.420 | 142.920 | 143.421 | 143.921 | 144.421 | 144.921 | 145.422 |
| 31      | 140.163 | 140.663 | 141.164 | 141.664 | 142.164 | 142.665 | 143.165 | 143.665 | 144.166 | 144.666 | 145.166 | 145.666 |
| 32      | 140.408 | 140.908 | 141.408 | 141.909 | 142.409 | 142.909 | 143.410 | 143.910 | 144.410 | 144.910 | 145.411 | 145.911 |
| 33      | 140.652 | 141.152 | 141.653 | 142.153 | 142.653 | 143.154 | 143.654 | 144.154 | 144.655 | 145.155 | 145.655 | 146.156 |
| 34      | 140.896 | 141.396 | 141.897 | 142.397 | 142.898 | 143.398 | 143.898 | 144.399 | 144.899 | 145.399 | 145.900 | 146.400 |
| 35      | 141.140 | 141.640 | 142.141 | 142.641 | 143.142 | 143.642 | 144.142 | 144.643 | 145.143 | 145.643 | 146.144 | 146.644 |
| 36      | 141.384 | 141.884 | 142.385 | 142.885 | 143.386 | 143.886 | 144.386 | 144.887 | 145.387 | 145.887 | 146.388 | 146.888 |
| 37      | 141.628 | 142.128 | 142.628 | 143.129 | 143.629 | 144.130 | 144.630 | 145.131 | 145.631 | 146.131 | 146.632 | 147.132 |
| 38      | 141.871 | 142.372 | 142.872 | 143.372 | 143.873 | 144.373 | 144.874 | 145.374 | 145.875 | 146.375 | 146.875 | 147.376 |
| 39      | 142.114 | 142.615 | 143.115 | 143.616 | 144.116 | 144.617 | 145.117 | 145.618 | 146.118 | 146.619 | 147.119 | 147.619 |
| 40      | 142.358 | 142.858 | 143.359 | 143.859 | 144.360 | 144.860 | 145.361 | 145.861 | 146.362 | 146.862 | 147.362 | 147.863 |
| 41      | 142.601 | 143.101 | 143.602 | 144.102 | 144.603 | 145.103 | 145.604 | 146.104 | 146.605 | 147.105 | 147.606 | 148.106 |
| 42      | 142.844 | 143.344 | 143.845 | 144.345 | 144.846 | 145.346 | 145.847 | 146.347 | 146.848 | 147.348 | 147.849 | 148.349 |
| 43      | 143.086 | 143.587 | 144.087 | 144.588 | 145.089 | 145.589 | 146.090 | 146.590 | 147.091 | 147.591 | 148.092 | 148.592 |
| 44      | 143.329 | 143.829 | 144.330 | 144.831 | 145.331 | 145.832 | 146.332 | 146.833 | 147.334 | 147.834 | 148.335 | 148.835 |
| 45      | 143.571 | 144.072 | 144.573 | 145.073 | 145.574 | 146.074 | 146.575 | 147.076 | 147.576 | 148.077 | 148.577 | 149.078 |
| 46      | 143.814 | 144.314 | 144.815 | 145.316 | 145.816 | 146.317 | 146.817 | 147.318 | 147.819 | 148.319 | 148.820 | 149.320 |
| 47      | 144.056 | 144.556 | 145.057 | 145.558 | 146.058 | 146.559 | 147.060 | 147.560 | 148.061 | 148.562 | 149.062 | 149.563 |
| 48      | 144.298 | 144.798 | 145.299 | 145.800 | 146.300 | 146.801 | 147.302 | 147.803 | 148.303 | 148.804 | 149.305 | 149.805 |
| 49      | 144.540 | 145.040 | 145.541 | 146.042 | 146.542 | 147.043 | 147.544 | 148.045 | 148.545 | 149.046 | 149.547 | 150.047 |
| 50      | 144.781 | 145.282 | 145.783 | 146.283 | 146.784 | 147.285 | 147.786 | 148.286 | 148.787 | 149.288 | 149.789 | 150.289 |
| 51      | 145.023 | 145.524 | 146.024 | 146.525 | 147.026 | 147.527 | 148.027 | 148.528 | 149.029 | 149.530 | 150.030 | 150.531 |
| 52      | 145.264 | 145.765 | 146.266 | 146.767 | 147.267 | 147.768 | 148.269 | 148.770 | 149.271 | 149.771 | 150.272 | 150.773 |
| 53      | 145.505 | 146.006 | 146.507 | 147.008 | 147.509 | 148.010 | 148.510 | 149.011 | 149.512 | 150.013 | 150.514 | 151.014 |
| 54      | 145.747 | 146.247 | 146.748 | 147.249 | 147.750 | 148.251 | 148.752 | 149.252 | 149.753 | 150.254 | 150.755 | 151.256 |
| 55      | 145.987 | 146.488 | 146.989 | 147.490 | 147.991 | 148.492 | 148.993 | 149.494 | 149.995 | 150.495 | 150.996 | 151.497 |
| 56      | 146.228 | 146.729 | 147.230 | 147.731 | 148.232 | 148.733 | 149.234 | 149.735 | 150.236 | 150.736 | 151.237 | 151.738 |
| 57      | 146.469 | 146.970 | 147.471 | 147.972 | 148.473 | 148.974 | 149.475 | 149.976 | 150.476 | 150.977 | 151.478 | 151.979 |
| 58      | 146.709 | 147.210 | 147.711 | 148.212 | 148.713 | 149.214 | 149.715 | 150.216 | 150.717 | 151.218 | 151.719 | 152.220 |
| 59      | 146.950 | 147.451 | 147.952 | 148.453 | 148.954 | 149.455 | 149.956 | 150.457 | 150.958 | 151.459 | 151.960 | 152.461 |
| 60      | 147.190 | 147.691 | 148.192 | 148.693 | 149.194 | 149.695 | 150.196 | 150.697 | 151.198 | 151.699 | 152.200 | 152.701 |
| 61      | 147.430 | 147.931 | 148.432 | 148.933 | 149.435 | 149.936 | 150.437 | 150.938 | 151.439 | 151.940 | 152.441 | 152.942 |
| 62      | 147.670 | 148.171 | 148.672 | 149.174 | 149.675 | 150.176 | 150.677 | 151.178 | 151.679 | 152.180 | 152.681 | 153.182 |
| 63      | 147.910 | 148.411 | 148.912 | 149.413 | 149.915 | 150.416 | 150.917 | 151.418 | 151.919 | 152.420 | 152.921 | 153.422 |
| 64      | 148.150 | 148.651 | 149.152 | 149.653 | 150.154 | 150.656 | 151.157 | 151.658 | 152.159 | 152.660 | 153.161 | 153.662 |
| 65      | 148.389 | 148.890 | 149.392 | 149.893 | 150.394 | 150.895 | 151.396 | 151.898 | 152.399 | 152.900 | 153.401 | 153.902 |
| 66      | 148.629 | 149.130 | 149.631 | 150.132 | 150.634 | 151.135 | 151.636 | 152.137 | 152.638 | 153.140 | 153.641 | 154.142 |
| 67      | 148.868 | 149.369 | 149.870 | 150.372 | 150.873 | 151.374 | 151.876 | 152.377 | 152.878 | 153.379 | 153.880 | 154.382 |
| 68      | 149.107 | 149.608 | 150.110 | 150.611 | 151.112 | 151.614 | 152.115 | 152.616 | 153.117 | 153.619 | 154.120 | 154.621 |
| 69      | 149.346 | 149.847 | 150.349 | 150.850 | 151.351 | 151.853 | 152.354 | 152.855 | 153.357 | 153.858 | 154.359 | 154.860 |
| 70      | 149.585 | 150.086 | 150.588 | 151.089 | 151.590 | 152.092 | 152.593 | 153.094 | 153.596 | 154.097 | 154.598 | 155.100 |

Table 42 (Cont.)

| N1 - N2 | NB - N1 |         |         |         |         |         |         |         |         |         |         |         |
|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
|         | 277     | 278     | 279     | 280     | 281     | 282     | 283     | 284     | 285     | 286     | 287     | 288     |
| 1       | 138.750 | 139.250 | 139.750 | 140.250 | 140.750 | 141.250 | 141.750 | 142.250 | 142.750 | 143.250 | 143.750 | 144.250 |
| 2       | 139.000 | 139.500 | 140.000 | 140.500 | 141.000 | 141.500 | 142.000 | 142.500 | 143.000 | 143.500 | 144.000 | 144.500 |
| 3       | 139.249 | 139.749 | 140.249 | 140.749 | 141.249 | 141.749 | 142.249 | 142.749 | 143.249 | 143.749 | 144.249 | 144.749 |
| 4       | 139.499 | 139.999 | 140.499 | 140.999 | 141.499 | 141.999 | 142.499 | 142.999 | 143.499 | 143.999 | 144.499 | 144.999 |
| 5       | 139.748 | 140.248 | 140.748 | 141.248 | 141.748 | 142.248 | 142.748 | 143.248 | 143.748 | 144.248 | 144.748 | 145.248 |
| 6       | 139.997 | 140.497 | 140.997 | 141.497 | 141.997 | 142.497 | 142.997 | 143.497 | 143.997 | 144.497 | 144.997 | 145.497 |
| 7       | 140.246 | 140.746 | 141.246 | 141.746 | 142.246 | 142.746 | 143.246 | 143.746 | 144.246 | 144.746 | 145.246 | 145.746 |
| 8       | 140.494 | 140.994 | 141.494 | 141.994 | 142.494 | 142.994 | 143.494 | 143.994 | 144.494 | 144.994 | 145.494 | 145.994 |
| 9       | 140.743 | 141.243 | 141.743 | 142.243 | 142.743 | 143.243 | 143.743 | 144.243 | 144.743 | 145.243 | 145.743 | 146.243 |
| 10      | 140.991 | 141.491 | 141.991 | 142.491 | 142.991 | 143.491 | 143.991 | 144.491 | 144.991 | 145.491 | 145.991 | 146.491 |
| 11      | 141.239 | 141.739 | 142.239 | 142.739 | 143.239 | 143.739 | 144.239 | 144.739 | 145.239 | 145.739 | 146.240 | 146.740 |
| 12      | 141.487 | 141.987 | 142.487 | 142.987 | 143.487 | 143.987 | 144.487 | 144.987 | 145.487 | 145.988 | 146.488 | 146.988 |
| 13      | 141.735 | 142.235 | 142.735 | 143.235 | 143.735 | 144.235 | 144.735 | 145.235 | 145.735 | 146.235 | 146.735 | 147.235 |
| 14      | 141.983 | 142.483 | 142.983 | 143.483 | 143.983 | 144.483 | 144.983 | 145.483 | 145.983 | 146.483 | 146.983 | 147.483 |
| 15      | 142.230 | 142.730 | 143.230 | 143.730 | 144.230 | 144.730 | 145.230 | 145.730 | 146.231 | 146.731 | 147.231 | 147.731 |
| 16      | 142.477 | 142.977 | 143.477 | 143.977 | 144.478 | 144.978 | 145.478 | 145.978 | 146.478 | 146.978 | 147.478 | 147.978 |
| 17      | 142.724 | 143.224 | 143.725 | 144.225 | 144.725 | 145.225 | 145.725 | 146.225 | 146.725 | 147.225 | 147.725 | 148.225 |
| 18      | 142.971 | 143.471 | 143.971 | 144.472 | 144.972 | 145.472 | 145.972 | 146.472 | 146.972 | 147.472 | 147.972 | 148.472 |
| 19      | 143.218 | 143.718 | 144.218 | 144.718 | 145.219 | 145.719 | 146.219 | 146.719 | 147.219 | 147.719 | 148.219 | 148.719 |
| 20      | 143.465 | 143.965 | 144.465 | 144.965 | 145.465 | 145.965 | 146.465 | 146.966 | 147.466 | 147.966 | 148.466 | 148.966 |
| 21      | 143.711 | 144.211 | 144.711 | 145.212 | 145.712 | 146.212 | 146.712 | 147.212 | 147.712 | 148.212 | 148.712 | 149.213 |
| 22      | 143.957 | 144.458 | 144.958 | 145.458 | 145.958 | 146.458 | 146.958 | 147.458 | 147.959 | 148.459 | 148.959 | 149.459 |
| 23      | 144.204 | 144.704 | 145.204 | 145.704 | 146.204 | 146.704 | 147.204 | 147.705 | 148.205 | 148.705 | 149.205 | 149.705 |
| 24      | 144.449 | 144.950 | 145.450 | 145.950 | 146.450 | 146.950 | 147.451 | 147.951 | 148.451 | 148.951 | 149.451 | 149.951 |
| 25      | 144.695 | 145.195 | 145.696 | 146.196 | 146.696 | 147.196 | 147.696 | 148.197 | 148.697 | 149.197 | 149.697 | 150.197 |
| 26      | 144.941 | 145.441 | 145.941 | 146.442 | 146.942 | 147.442 | 147.942 | 148.442 | 148.943 | 149.443 | 149.943 | 150.443 |
| 27      | 145.186 | 145.687 | 146.187 | 146.687 | 147.187 | 147.687 | 148.188 | 148.688 | 149.188 | 149.688 | 150.189 | 150.689 |
| 28      | 145.432 | 145.932 | 146.432 | 146.932 | 147.433 | 147.933 | 148.433 | 148.933 | 149.434 | 149.934 | 150.434 | 150.934 |
| 29      | 145.677 | 146.177 | 146.677 | 147.178 | 147.678 | 148.178 | 148.678 | 149.179 | 149.679 | 150.179 | 150.679 | 151.180 |
| 30      | 145.922 | 146.422 | 146.922 | 147.423 | 147.923 | 148.423 | 148.923 | 149.424 | 149.924 | 150.424 | 150.924 | 151.425 |
| 31      | 146.167 | 146.667 | 147.167 | 147.668 | 148.168 | 148.668 | 149.168 | 149.669 | 150.169 | 150.669 | 151.169 | 151.670 |
| 32      | 146.411 | 146.912 | 147.412 | 147.912 | 148.413 | 148.913 | 149.413 | 149.913 | 150.414 | 150.914 | 151.414 | 151.915 |
| 33      | 146.656 | 147.156 | 147.657 | 148.157 | 148.657 | 149.158 | 149.658 | 150.158 | 150.658 | 151.159 | 151.659 | 152.159 |
| 34      | 146.900 | 147.401 | 147.901 | 148.401 | 148.902 | 149.402 | 149.902 | 150.403 | 150.903 | 151.403 | 151.904 | 152.404 |
| 35      | 147.145 | 147.645 | 148.145 | 148.646 | 149.146 | 149.646 | 150.147 | 150.647 | 151.147 | 151.648 | 152.148 | 152.648 |
| 36      | 147.389 | 147.889 | 148.389 | 148.890 | 149.390 | 149.890 | 150.391 | 150.891 | 151.392 | 151.892 | 152.392 | 152.893 |
| 37      | 147.633 | 148.133 | 148.633 | 149.134 | 149.634 | 150.134 | 150.635 | 151.135 | 151.636 | 152.136 | 152.636 | 153.137 |
| 38      | 147.876 | 148.377 | 148.877 | 149.378 | 149.878 | 150.378 | 150.879 | 151.379 | 151.880 | 152.380 | 152.880 | 153.381 |
| 39      | 148.120 | 148.620 | 149.121 | 149.621 | 150.122 | 150.622 | 151.123 | 151.623 | 152.123 | 152.624 | 153.124 | 153.625 |
| 40      | 148.363 | 148.864 | 149.364 | 149.865 | 150.365 | 150.866 | 151.366 | 151.867 | 152.367 | 152.867 | 153.368 | 153.868 |
| 41      | 148.607 | 149.107 | 149.608 | 150.108 | 150.609 | 151.109 | 151.610 | 152.110 | 152.610 | 153.111 | 153.611 | 154.112 |
| 42      | 148.850 | 149.350 | 149.851 | 150.351 | 150.852 | 151.352 | 151.853 | 152.353 | 152.854 | 153.354 | 153.855 | 154.355 |
| 43      | 149.093 | 149.593 | 150.094 | 150.594 | 151.095 | 151.595 | 152.096 | 152.597 | 153.097 | 153.598 | 154.098 | 154.598 |
| 44      | 149.336 | 149.836 | 150.337 | 150.837 | 151.338 | 151.838 | 152.339 | 152.840 | 153.340 | 153.841 | 154.341 | 154.842 |
| 45      | 149.579 | 150.079 | 150.580 | 151.080 | 151.581 | 152.081 | 152.582 | 153.082 | 153.583 | 154.084 | 154.584 | 155.085 |
| 46      | 149.821 | 150.322 | 150.822 | 151.323 | 151.823 | 152.324 | 152.825 | 153.325 | 153.826 | 154.326 | 154.827 | 155.327 |
| 47      | 150.064 | 150.564 | 151.065 | 151.565 | 152.066 | 152.567 | 153.067 | 153.568 | 154.068 | 154.569 | 155.070 | 155.570 |
| 48      | 150.306 | 150.806 | 151.307 | 151.808 | 152.308 | 152.809 | 153.310 | 153.810 | 154.311 | 154.811 | 155.312 | 155.813 |
| 49      | 150.548 | 151.049 | 151.549 | 152.050 | 152.551 | 153.051 | 153.552 | 154.053 | 154.553 | 155.054 | 155.554 | 156.055 |
| 50      | 150.790 | 151.291 | 151.791 | 152.292 | 152.793 | 153.293 | 153.794 | 154.295 | 154.795 | 155.296 | 155.797 | 156.297 |
| 51      | 151.032 | 151.533 | 152.033 | 152.534 | 153.035 | 153.535 | 154.036 | 154.537 | 155.037 | 155.538 | 156.039 | 156.540 |
| 52      | 151.274 | 151.774 | 152.275 | 152.776 | 153.277 | 153.777 | 154.278 | 154.779 | 155.279 | 155.780 | 156.281 | 156.782 |
| 53      | 151.515 | 152.016 | 152.517 | 153.017 | 153.518 | 154.019 | 154.520 | 155.020 | 155.521 | 156.022 | 156.523 | 157.023 |
| 54      | 151.757 | 152.257 | 152.758 | 153.259 | 153.760 | 154.261 | 154.761 | 155.262 | 155.763 | 156.264 | 156.764 | 157.265 |
| 55      | 151.998 | 152.499 | 153.000 | 153.500 | 154.001 | 154.502 | 155.003 | 155.504 | 156.004 | 156.505 | 157.006 | 157.507 |
| 56      | 152.239 | 152.740 | 153.241 | 153.742 | 154.242 | 154.743 | 155.244 | 155.745 | 156.246 | 156.747 | 157.247 | 157.748 |
| 57      | 152.480 | 152.981 | 153.482 | 153.983 | 154.484 | 154.984 | 155.485 | 155.986 | 156.487 | 156.988 | 157.489 | 157.989 |
| 58      | 152.721 | 153.222 | 153.723 | 154.224 | 154.725 | 155.225 | 155.726 | 156.227 | 156.728 | 157.229 | 157.730 | 158.231 |
| 59      | 152.962 | 153.463 | 153.964 | 154.464 | 154.965 | 155.466 | 155.967 | 156.468 | 156.969 | 157.470 | 157.971 | 158.472 |
| 60      | 153.202 | 153.703 | 154.204 | 154.705 | 155.206 | 155.707 | 156.208 | 156.709 | 157.210 | 157.711 | 158.212 | 158.713 |
| 61      | 153.443 | 153.944 | 154.445 | 154.946 | 155.447 | 155.948 | 156.449 | 156.950 | 157.451 | 157.952 | 158.452 | 158.953 |
| 62      | 153.683 | 154.184 | 154.685 | 155.186 | 155.687 | 156.188 | 156.689 | 157.190 | 157.691 | 158.192 | 158.693 | 159.194 |
| 63      | 153.923 | 154.424 | 154.925 | 155.426 | 155.928 | 156.429 | 156.930 | 157.431 | 157.932 | 158.433 | 158.934 | 159.435 |
| 64      | 154.163 | 154.664 | 155.166 | 155.667 | 156.168 | 156.669 | 157.170 | 157.671 | 158.172 | 158.673 | 159.174 | 159.675 |
| 65      | 154.403 | 154.904 | 155.406 | 155.907 | 156.408 | 156.909 | 157.410 | 157.911 | 158.412 | 158.913 | 159.414 | 159.915 |
| 66      | 154.643 | 155.144 | 155.645 | 156.147 | 156.648 | 157.149 | 157.650 | 158.151 | 158.652 | 159.153 | 159.654 | 160.155 |
| 67      | 154.883 | 155.384 | 155.885 | 156.386 | 156.887 | 157.389 | 157.890 | 158.391 | 158.892 | 159.393 | 159.894 | 160.395 |
| 68      | 155.122 | 155.624 | 156.125 | 156.626 | 157.127 | 157.628 | 158.130 | 158.631 | 159.132 | 159.633 | 160.134 | 160.635 |
| 69      | 155.362 | 155.863 | 156.364 | 156.865 | 157.367 | 157.868 | 158.369 | 158.870 | 159.371 | 159.873 | 160.374 | 160.875 |
| 70      | 155.601 | 156.102 | 156.604 | 157.105 | 157.606 | 158.107 | 158.609 | 159.110 | 159.611 | 160.112 | 160.613 | 161.115 |