

NEOPRENE  
3/16 & 1/4 DIAMETER

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

**> MATERIAL:**


Neoprene  
Approx. 70 durometer compounded for use in mechanical belt drives

**> OPERATING TEMPERATURE:**

-65°F to +210°F

These belts can be used with Companion Pulleys and Grooved Pulleys, see index.

3% tolerance on circumference.  
10% elongation is permissible.



**INCH COMPONENT**

Catalog Number	I.D.
<b>3/16 Diameter</b>	
A 6R11-06102	3-1/4
A 6R11-06106	3-3/8
A 6R11-06110	3-1/2
A 6R11-06113	3-5/8
A 6R11-06118	3-3/4
A 6R11-06120	3-7/8
A 6R11-06126	4
A 6R11-06130	4-1/8
A 6R11-06134	4-1/4
A 6R11-06140	4-1/2
A 6R11-06151	4-3/4
A 6R11-06157	5
A 6R11-06160	5-1/8
A 6R11-06164	5-1/4
A 6R11-06171	5-1/2
A 6R11-06181	5-3/4
A 6R11-06184	5-7/8
A 6R11-06188	6
A 6R11-06196	6-1/4
A 6R11-06204	6-1/2
A 6R11-06212	6-3/4
A 6R11-06220	7
A 6R11-06228	7-1/4
A 6R11-06236	7-1/2
A 6R11-06243	7-3/4
A 6R11-06251	8
A 6R11-06259	8-1/4
A 6R11-06267	8-1/2
A 6R11-06275	8-3/4
A 6R11-06283	9
A 6R11-06291	9-1/4
A 6R11-06298	9-1/2
A 6R11-06306	9-3/4
A 6R11-06314	10
A 6R11-06330	10-1/2
A 6R11-06346	11
A 6R11-06361	11-1/2
A 6R11-06377	12
A 6R11-06408	13
A 6R11-06440	14
A 6R11-06471	15
A 6R11-06503	16
A 6R11-06534	17
A 6R11-06565	18

**INCH COMPONENT**

Catalog Number	I.D.
<b>3/16 Diameter</b>	
A 6R11-06597	19
A 6R11-06628	20
A 6R11-06660	21
A 6R11-06691	22
A 6R11-06723	23
A 6R11-06754	24
A 6R11-06785	25
A 6R11-06817	26
<b>1/4 Diameter</b>	
A 6R11-08141	4-1/2
A 6R11-08151	4-3/4
A 6R11-08157	5
A 6R11-08160	5-1/8
A 6R11-08165	5-1/4
A 6R11-08173	5-1/2
A 6R11-08181	5-3/4
A 6R11-08184	5-7/8
A 6R11-08188	6
A 6R11-08196	6-1/4
A 6R11-08204	6-1/2
A 6R11-08210	6-3/4
A 6R11-08220	7
A 6R11-08228	7-1/4
A 6R11-08236	7-1/2
A 6R11-08246	7-3/4
A 6R11-08255	8
A 6R11-08262	8-1/2
A 6R11-08280	9
A 6R11-08300	9-1/2
A 6R11-08314	10
A 6R11-08324	10-1/2
A 6R11-08346	11
A 6R11-08350	11-1/2
A 6R11-08380	12
A 6R11-08393	12-1/2
A 6R11-08408	13
A 6R11-08420	13-1/2
A 6R11-08440	14
A 6R11-08456	14-1/2
A 6R11-08470	15
A 6R11-08487	15-1/2
A 6R11-08503	16
A 6R11-08518	16-1/2
A 6R11-08524	17

**INCH COMPONENT**

Catalog Number	I.D.
<b>1/4 Diameter</b>	
A 6R11-08550	17-1/2
A 6R11-08565	18
A 6R11-08581	18-1/2
A 6R11-08590	19
A 6R11-08613	19-1/2
A 6R11-08628	20
A 6R11-08654	21
A 6R11-08691	22
A 6R11-08723	23
A 6R11-08754	24
A 6R11-08785	25

Continued from the previous page