


SELF-LUBRICATING

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

> **MATERIAL:**

Oil-Impregnated Bronze,
Self-Lubricating



METRIC COMPONENT

Catalog Number	d Bore H7	d Tolerance	D Dia.	D ₁ Dia. h11	D ₁ Tolerance	S Width 0 -0.3
A 7B 4MS04H908	4	+0.012/0	9.5	10	+0.034/+0.019	8
A 7B 4MS05H1210	5	+0.012/0	12.5	13	+0.041/+0.023	10
A 7B 4MS06H1411	6	+0.012/0	14.5	15	+0.041/+0.023	11
A 7B 4MS07H1511	7	+0.015/0	15.5	16	+0.041/+0.023	11
A 7B 4MS08H1511	8	+0.015/0	15.5	16	+0.041/+0.023	11
A 7B 4MS102114	10	+0.015/0	21	22	+0.049/+0.028	14
A 7B 4MS122416	12	+0.018/0	24	25	+0.049/+0.028	16

FELT WASHERS AND RETAINERS

SDP/SI

FOR SPHERICAL BEARINGS


PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

> MATERIAL:

Felt Washer - Felt, Oil-Impregnated (SAE 50)
Retainer - Steel, Spring



Bearing I.D. (mm)	X Nom. (Ref.)
3	1.35
4	1.65
5	2.1
6	2.3
7	2.45
8	2.45
9	3.05
10	2.75




METRIC COMPONENT

Catalog Number	d Dia.	D Dia.	S	Use With Bearing I.D. Δ
Felt Washer				
A 7B 4MW0810	7.6	10	3	3
A 7B 4MW1013	9.5	13	3	4
* A 7B 4MW1316	12.5	16	5	5
A 7B 4MW1518	14.5	18	5	6
A 7B 4MW1619	15.5	19	5	7 & 8
* A 7B 4MW1822	17.5	22	6	9
A 7B 4MW2127	21	27	6	10
A 7B 4MW2430	24	30	7	12

Catalog Number *	D ₁ Dia.	D ₂ Dia.	D ₃ Dia.	H Height	H ₁	Use with Bearing I.D. Δ
Retainer						
A 7B 4MR0715	14.92	9.5	6.5	1.05	0.2	3
A 7B 4MR1120	19.9	14.5	10.9	1.7	0.3	5
A 7B 4MR1224	23.9	17	12.4	2.15	0.3	6
A 7B 4MR1326	25.9	18	13.2	2.4	0.3	7 & 8
A 7B 4MR1532	31.9	19	15.1	2.25	0.35	9
A 7B 4MR1934	33.9	24	18.9	3.6	0.4	10

NOTE: Retainer for 12 mm Bearing I.D. not available.
 Δ For Spherical Bearings, see index.

* To be discontinued when present stock is depleted.



I
R
T
1
2
3
4
5
6
7
8
9
10
11
12
13
14
15
A