

PAN HEAD MACHINE SCREWS

SDP/SI


DIN 85

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

> MATERIAL:

304 Stainless Steel

Priced Per 100 Pieces



METRIC COMPONENT

Catalog Number	Thread Size	D Dia.	H	L Length	s	t
MD0085MXO020X006	M2	3.7	1.2	6	0.5	0.4
MD0085MXO020X010				10		
MD0085MXO025X006	M2.5	5	1.5	6	0.6	0.45
MD0085MXO025X008				8		
MD0085MXO025X010				10		
MD0085MXO025X012				12		
MD0085MXO025X016				16		
MD0085MXO025X020				20		
MD0085MXO025X025				25		
MD0085MXO030X006	M3	6	1.8	6	0.8	0.5
MD0085MXO030X008				8		
MD0085MXO030X016				16		
MD0085MXO030X020				20		
MD0085MXO030X030				30		
MD0085MXO040X006	M4	8	2.4	6	1	0.7
MD0085MXO040X010				10		
MD0085MXO040X012				12		
MD0085MXO040X016				16		
MD0085MXO040X020				20		
MD0085MXO040X025				25		
MD0085MXO040X030				30		
MD0085MXO050X008	M5	10	3	8	1.2	0.8
MD0085MXO050X010				10		
MD0085MXO050X012				12		
MD0085MXO050X016				16		
MD0085MXO050X020				20		
MD0085MXO050X025				25		
MD0085MXO050X030	30					
MD0085MXO060X012	M6	12	3.6	12	1.6	1
MD0085MXO060X030				30		

10-10
D805

I

R

T

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

A


DIN 84

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

► MATERIAL:

304 Stainless Steel

Priced Per 100 Pieces



- I
- R
- T
- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10**
- 11
- 12
- 13
- 14
- 15
- A

METRIC COMPONENT

Catalog Number	Thread Size	L Length	Catalog Number	Thread Size	L Length
MD0084MXO016X004	M1.6	4	MD0084MXO040X006	M4	6
MD0084MXO016X006		6	MD0084MXO040X008		8
MD0084MXO020X003		3	MD0084MXO040X010		10
MD0084MXO020X004	M2	4	MD0084MXO040X012		12
MD0084MXO020X005		5	MD0084MXO040X016		16
MD0084MXO020X006		6	MD0084MXO040X020		20
MD0084MXO020X008		8	MD0084MXO040X025		25
MD0084MXO020X010		10	MD0084MXO040X030		30
MD0084MXO020X016	16	MD0084MXO040X035	35		
MD0084MXO025X005	M2.5	5	MD0084MXO040X040		40
MD0084MXO025X006		6	MD0084MXO050X010	10	
MD0084MXO025X008		8	MD0084MXO050X012	12	
MD0084MXO025X010		10	MD0084MXO050X016	16	
MD0084MXO025X012		12	MD0084MXO050X020	20	
MD0084MXO025X016	16	MD0084MXO050X025	25		
MD0084MXO025X020	20	MD0084MXO050X030	30		
MD0084MXO030X005	M3	5	MD0084MXO050X035	35	
MD0084MXO030X006		6	MD0084MXO050X040	40	
MD0084MXO030X008		8	MD0084MXO060X008	8	
MD0084MXO030X010		10	MD0084MXO060X010	10	
MD0084MXO030X012		12	MD0084MXO060X012	12	
MD0084MXO030X020	20	MD0084MXO060X016	16		
MD0084MXO030X025	25	MD0084MXO060X020	20		
MD0084MXO035X008	M3.5	8	MD0084MXO060X025	25	
MD0084MXO035X012		12	MD0084MXO060X030	30	
MD0084MXO035X016		16			

Dimensions	Thread Size							
	M1.6	M2	M2.5	M3	M3.5	M4	M5	M6
t	0.35	0.4	0.45	0.5	0.6	0.7	0.8	1
D	3	3.8	4.5	5.5	6	7	8.5	10
H	1	1.3	1.6	2	2.5	2.6	3.3	3.6
s	0.4	0.5	0.6	0.8	0.9	1	1.2	1.6

FLAT HEAD MACHINE SCREWS


SDP/SI

DIN 963
90° FLAT HEAD

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

> **MATERIAL:**
304 Stainless Steel

Priced Per 100 Pieces



METRIC COMPONENT

Catalog Number	Thread Size	D Dia.	d (c'sink)	H	L Length	s	t
MD0963MXO020X004	M2	3.8	4.6	1.2	4	0.5	0.4
MD0963MXO020X005					5		
MD0963MXO020X006					6		
MD0963MXO020X008					8		
MD0963MXO020X010					10		
MD0963MXO020X012					12		
MD0963MXO025X004	M2.5	4.7	5.7	1.5	4	0.6	0.45
MD0963MXO025X006					6		
MD0963MXO025X008					8		
MD0963MXO025X010					10		
MD0963MXO025X012					12		
MD0963MXO025X016					16		
MD0963MXO025X020	20	M3	5.6	6.5	1.65	0.8	0.5
MD0963MXO030X005	5						
MD0963MXO030X006	6						
MD0963MXO030X008	8						
MD0963MXO030X010	10						
MD0963MXO030X012	12						
MD0963MXO030X016	16						
MD0963MXO030X020	20						
MD0963MXO030X025	25						

I

R

T

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

A

10-12
D805