



A. SHAFTS	
1.0 introduction	T12
2.0 Determination Of Stresses For Solid Cylindrical Shafts	T12
3.0 Hollow Cylindrical Shafts	T15
B. POROUS-METAL BEARINGS	
1.0 General Properties	T16
2.0 Sizing Porous-Metal Bearings	T17
3.0 Clearances	T17
4.0 Press Fits	T19
5.0 Conclusion	T22
C. PLASTIC AND NON-METALLIC BEARINGS	
1.0 General Characteristics	T23
2.0 Properties Of Plastic And Non-Metallic Bearing Materials	T23
3.0 Sizing Plastic And Non-Metallic Bearings	T27
4.0 Conclusion	T28
D. BALL BEARINGS	
1.0 introduction	T29
2.0 Types of Ball Bearings	T29
3.0 Bearing Selection	T31
4.0 Bearing Loads	T31
5.0 Sizing Ball Bearings	T41
6.0 Tolerances And Clearances...	T43
E. COUPLINGS	
1.0 Introduction	T49
2.0 Application Considerations	T49
3.0 Types of Flexible Couplings	T51
3.1 Universal Joints	T51
3.2 Oldham Couplings	T52
3.3 Flexible Shafts	T53
3.4 Miscellaneous Couplings	T55
F. UNIVERSAL JOINTS	
1.0 General	T58
2.0 Applications	T58
3.0 General Characteristics Of The Cardan Joint	T58
4.0 Kinematics	T59
4.1 Example 1: Determining the Maximum Inertia Torque	T60
5.0 Joint Selection (Torque Rating)	T62
5.1 Example 2: Universal Joint Selection for Continuous Operation	T63
5.2 Example 3: Universal Joint Selection for intermittent Operation with Shock Loading	T63
5.3 Example 4: Determining the Maximum Speed of an Input Shaft	T63
6.0 Secondary Couples	T64
7.0 Joints in Series	T64
7.1 Phasing	T65
7.2 Example 5: Determining the Maximum Speed of an Input Shaft in a Series	T65
7.3 Example 6	T65
G. REFERENCE TABLE INDEX 167	T67