


## 5 – Right Angle Drives

### Helical Gear Drives (Hollow Shafts)

1:1, 2:1 and  
3:2 Ratios  
pg 5-3 thru 5-5

INCH SIZES



### Helical Gear Drives 2-, 3-, 4- Shafts

1:1 Ratio  
pg 5-6


INCH SIZES



### Foot Mounts for 2-, 3-, 4- Shaft Units

pg 5-7


INCH SIZES



### Light-Duty Right Angle and Dual Helical Gear Drives

1:1 Ratio  
Standard or Panel Mounted  
pg 5-8 thru 5-11


INCH & METRIC SIZES



### Light-Duty Helical Gear Speed Reducers

1:1 to 25:1 Ratios  
Panel and Base Mounted  
pg 5-12 thru 5-15


INCH & METRIC SIZES



### Heavy-Duty Right Angle and Dual Helical Drives

1:1 Ratio  
pg 5-16

INCH SIZES






# 5 – Right Angle Drives




**Precision  
Worm Gear  
Speed Reducers**  
20:1 to 120:1 Ratios  
pg 5–17




**INCH SIZES**

**Precision  
Worm Gear  
Drives, Style “E”**  
6:1 to 100:1 Ratios  
pg 5–18 thru pg 5–23




**INCH & METRIC SIZES**

**Commercial  
Worm Gear  
Drives**  
(Solid and  
Hollow Shafts)  
3.5:1 to 60:1 Ratios  
pg 5–24



**INCH SIZES**

**Worm  
Gear Drives**  
5:1, 10:1, 20:1 Ratios  
**Bevel  
Gear Drives**  
1:1, 2:1, 3:1 Ratios  
pg 5–25




**INCH SIZES**

**Precision  
Heavy-Duty Spiral  
Bevel Gear Drives**  
“L” and  
“T” Style  
1:1 and 2:1 Ratios  
pg 5–26 thru 5–28




**METRIC SIZES**

**Precision  
Bevel  
Gear Drives**  
1:1 Ratio  
pg 5–29




**METRIC SIZES**

**Low-Cost  
Bevel  
Gear  
Drives**  
Economy Series  
1:1 and 2:1 Ratios  
pg 5–30 and 5–31



**METRIC SIZES**

**Bevel Gear  
Drives**  
Metal and  
Plastic Gears  
1:1, 2:1 and  
3:1 Ratios  
pg 5–32 thru 5–37



**INCH & METRIC SIZES**



<b>PICTORIAL GUIDE TO RIGHT ANGLE DRIVES</b> .....	5-0
<b>HELICAL GEAR DRIVES – Hollow Shafts</b>	
1:1 Ratio – Mini (Inch) .....	5-3
2:1 Ratio (Inch) .....	5-4
1:1 and 3:2 Ratio (Inch) .....	5-5
<b>HELICAL GEAR DRIVES – 1:1 Ratio</b>	
2-, 3-, 4- Shafts (Inch) .....	5-6
Foot Mounts (Inch) .....	5-7
<b>RIGHT ANGLE and DUAL HELICAL GEAR DRIVES – 1:1 Ratio</b>	
Light-Duty (Inch and Metric) .....	5-8
Panel Mounted (Inch and Metric) .....	5-10
<b>HELICAL GEAR SPEED REDUCERS – 1:1 thru 25:1 Ratios</b>	
Panel Mounted (Inch and Metric) .....	5-12
Base Mounted (Inch and Metric) .....	5-14
<b>RIGHT ANGLE and DUAL HELICAL GEAR DRIVES – 1:1 Ratio</b>	
Heavy-Duty (Inch) .....	5-16
<b>WORM GEAR SPEED REDUCERS – 20:1 thru 120:1 Ratios</b>	
Precision Quality – Permanantly Lubricated (Inch) .....	5-17
<b>WORM GEAR SPEED REDUCERS – 6:1 thru 100:1 Ratios</b>	
Precision Quality – Style “E” (Inch and Metric) .....	5-18
<b>WORM GEAR SPEED REDUCERS – 3.5:1 thru 60:1 Ratios</b>	
Solid and Hollow Shafts (Inch) .....	5-24
<b>WORM GEAR DRIVES – 5:1, 10:1 and 20:1 Ratios (Inch) .....</b>	5-25
<b>BEVEL GEAR DRIVES – 1:1, 2:1 and 3:1 Ratios (Inch) .....</b>	5-25
<b>HEAVY-DUTY BEVEL GEAR DRIVES – 1:1 and 2:1 Ratios</b>	
“L” (Metric) .....	5-26
“T” (Metric) .....	5-27
Capabilities .....	5-28
<b>BEVEL GEAR DRIVES – 1:1 Ratio (Metric) .....</b>	5-29
<b>ECONOMY SERIES BEVEL GEAR DRIVES</b>	
1:1 Ratio (Metric) .....	5-30
2:1 Ratio (Metric) .....	5-31
<b>BEVEL GEAR DRIVES</b>	
1:1, 2:1 and 3:1 Ratios (Inch and Metric) .....	5-32
1:1 and 2:1 Ratios (Inch and Metric) .....	5-34
1:1 Ratio (Large) (Inch and Metric) .....	5-36