



HANDBOOK OF TIMING BELTS AND PULLEYS

The **Technical Section** of this catalog is the result of close cooperation of Stock Drive Products/Sterling Instrument staff with experts in the fields of power transmission design and manufacturing. We wish, therefore, to recognize the contribution of the following company and individuals:

THE GATES RUBBER COMPANY, that provided the material contained in their publication 17183.

Staff of Stock Drive Products/Sterling Instrument:

Dr. Frank Buchsbaum, Executive Vice President, Designatronics, Inc.
 Dr. Hitoshi Tanaka, Senior Vice President, Designatronics, Inc.
 Robbie Robinson, Manager, New Products and Technology
 Julia Nelson, Application Engineer
 Linda Shuett, Graphic Communications Manager
 Milton Epstein, Assistant Editor
 John Chiamonte and Mary McKenna, Graphic Artists

... and many others on the staff who individually and collectively spent their time and effort that resulted in publication of this text.

No part of this publication may be reproduced in any form or by any means without the prior written permission of the Company. This does not cover material which was attributed to another publication.

HANDBOOK OF TIMING BELTS & PULLEYS

Table of Contents

	Page
SECTION 1 INTRODUCTION	T-3
SECTION 2 GATES POWERGRIP® GT® BELT DRIVES	T-4
SECTION 3 COMPARISON GRAPHS	T-6
SECTION 4 DRIVE COMPARATIVE STUDIES	T-8
4.1 Durability	T-8
4.2 Tooth Jump Resistance	T-8
4.3 Noise	T-9
4.4 Positioning Accuracy	T-9
SECTION 5 DIFFERENT BELT CONFIGURATIONS	T-10
5.1 Double-Sided Twin Power® Belt Drives	T-10
5.2 Long Length Timing Belt Stock	T-10
SECTION 6 BELT CONSTRUCTION	T-10
6.1 Characteristics Of Reinforcing Fibers	T-11
6.2 Cord Twist And Its Effect On The Drive	T-12
6.3 Factors Contributing To Side Travel	T-13
6.4 Characteristics Of Belt Body Materials	T-14
SECTION 7 BELT TOOTH PROFILES	T-15
SECTION 8 PULLEY PITCH AND OUTSIDE DIAMETERS	T-16
SECTION 9 DESIGN AND INSTALLATION SUGGESTIONS	T-42
9.1 Low-Speed Operation	T-43
9.2 High-Speed Operation	T-43
9.3 Smooth Running	T-44
9.4 Drive Noise	T-44
9.5 Static Conductivity	T-45
9.6 Operating Environments	T-45
9.7 Belt Tracking	T-47
9.8 Pulley Flanging	T-48
9.9 Registration	T-49
SECTION 10 BELT TENSIONING	T-50
10.1 What Is Proper Installation Tension	T-50
10.2 Making Measurements	T-52
SECTION 11 DRIVE ALIGNMENT	T-53
11.1 Angular And Parallel	T-53
11.2 Practical Tips	T-54
SECTION 12 INSTALLATION AND TAKE-UP	T-54
12.1 Installation Allowance	T-54

12.2 Belt Installation T-54

12.3 Belt Take-up T-55

12.4 Fixed Center Drives T-55

SECTION 13 IDLER USAGE T-56

13.1 Inside/Outside T-56

13.2 Tight Side/Slack Side T-56

13.3 Idler Placement T-56

13.4 Spring-Loaded Idlers T-56

13.5 Size Recommendations T-57

13.6 Specifying Shaft Locations In Multipoint Drive Layouts T-57

SECTION 14 BELT PULL AND BEARING LOADS T-58

14.1 Motion Transfer Drives T-59

14.2 Power Transmission Drives T-59

14.3 Registration Drives T-60

14.4 Bearing Load Calculations T-60

SECTION 15 HANDLING AND STORAGE T-61

SECTION 16 STANDARDS APPLICABLE TO BELTS T-61

SECTION 17 STANDARDS APPLICABLE TO PULLEYS AND FLANGES T-63

17.1 Pulley Tolerances T-64

17.2 Pulley Materials T-67

17.3 Flange Design And Face Width Guidelines T-67

17.4 Guidelines For PowerGrip® GT®2 Flange Design T-68

SECTION 18 DOUBLE-SIDED TWIN POWER® BELT TOLERANCES T-69

SECTION 19 LONG LENGTH TIMING BELT STOCK SPECIFICATIONS T-70

SECTION 20 DESIGN AIDS ON INTERNET (www.sdp-si.com) T-71

SECTION 21 DRIVE RATIO TABLES T-72

SECTION 22 CENTER DISTANCE FORMULAS T-79

22.1 Nomenclature And Basic Equations T-79

22.2 Exact Center Distance Determination – Unequal Pulleys T-79

22.3 Exact Center Distance Determination – Equal Pulleys T-80

22.4 Approximate Center Distance Determination T-80

22.5 Number Of Teeth In Mesh (TIM) T-80

22.6 Determination Of Belt Size For Given Pulleys And Center Distance T-81

SECTION 23 CENTER DISTANCE FACTOR TABLES (Table 39) T-81

SECTION 24 TIMING BELT DRIVE SELECTION PROCEDURE T-146

LIST OF TABLES T-168

LIST OF FIGURES T-170