

Table 53 List of Tables

Table	Table Description	Page
1	Comparison of Different Tension Member Materials	T-12
2	Comparison of Different Belt Body Materials	T-14
3	Allowable Working Tension of Different Belt Constructions	T-15
4	Basic Belt Dimensions	T-16
5	.080" (2.03 mm) MXL Pitch Pulley Dimensions	T-18
6	40 D.P. (2.07 mm) Pitch Pulley Dimensions	T-20
7	1/5" (5.08 mm) XL Pitch Pulley Dimensions	T-22
8	3/8" (9.525 mm) L Pitch Pulley Dimensions	T-24
9	3 mm Pitch HTD Pulley Dimensions	T-26
10	5 mm Pitch HTD Pulley Dimensions	T-28
11	8 mm Pitch HTD Pulley Dimensions	T-30
12	2 mm Pitch GT2 Pulley Dimensions	T-32
13	3 mm Pitch GT2 Pulley Dimensions	T-34
14	5 mm Pitch GT2 Pulley Dimensions	T-36
15	T2.5 (2.5 mm) Pitch Pulley Dimensions	T-38
16	T5 (5 mm) Pitch Pulley Dimensions	T-39
17	T10 (10 mm) Pitch Pulley Dimensions	T-40
18	Minimum Pulley Diameters	T-41
19	Belt Tensioning Force	T-51
20	Static Belt Tension, T_{st} (lbs) Per Span – General Values	T-51
21	Idler Size Recommendations	T-57
22	Recommended Tension for Length Measurement	T-62
23	Belt Width Tolerances	T-62
24	Pitch Length Tolerances	T-62
25	Center Distance Tolerances	T-63
26	Overall Belt Thickness Dimensions	T-63
27	Overall Belt Thickness Tolerances	T-63

Continued on the next page

Table 53 (Cont.) List of Tables

Table	Table Description	Page
28	Pulley O.D. Tolerances	T-64
29	Pulley Eccentricity	T-64
30	Bore Tolerance for Pulleys	T-65
31	Pulley Pitch Accuracy	T-65
32	ISO Axial Pulley Runout	T-65
33	ISO Radial Pulley Runout	T-65
34	ISO Pulley O.D. Tolerances	T-66
35	RMA Pulley Bore Tolerances	T-66
36	Nominal Flange Dimensions for Molding, Sintering, Casting, etc.	T-68
37	Additional Amount of Face Width Recommended over Nominal Belt Width	T-68
38	Belt Thickness Tolerances	T-69
39	Center Distance Tolerances	T-69
40	PowerGrip Long-Length Belting Specifications	T-70
41	Drive Ratio Tables	T-74
42	Center Distance Factor Tables	T-81
43	Rated Torque for Small Pulleys – 2 mm Pitch GT2 Belts	T-152
44	Rated Torque for Small Pulleys – 3 mm Pitch GT2 Belts	T-154
45	Rated Torque for Small Pulleys – 5 mm Pitch GT2 Belts	T-156
46	Rated Horsepower for Small Pulleys – 5 mm Pitch GT2 Belts	T-158
47	Rated Torque for Small Pulleys – 3 mm Pitch HTD Belts	T-160
48	Rated Torque for Small Pulleys – 5 mm Pitch HTD Belts	T-162
49	Rated Torque for Small Pulleys – MXL (.080") Pitch Belts	T-164
50	Rated Torque for Small Pulleys – XL (.200") Pitch Belts	T-165
51	Rated Horsepower for Small Pulleys – T5 mm Pitch Belts	T-166
52	Rated Horsepower for Small Pulleys – T10 mm Pitch Belts	T-167
53	List of Tables	T-168
54	List of Figures	T-170

Table 54 List of Figures

Figure	Figure Description	Page
1	Pulley and Belt Geometry	T-3
2	Stress Pattern in Belts	T-4
3	Comparison of Different Tooth Profiles	T-4
4	Comparative Belt Pitch Selection Guide	T-6
5	Horsepower Ratings at High Speed	T-7
6	Horsepower Ratings at Low Speed	T-7
7	Comparison of Performance Ratios for Various Belts	T-8
8	Comparison of Tooth Jump Torques for Various Belts	T-8
9	Comparison of Noise Levels for Various Belts	T-9
10	Comparison of Positioning Errors of Various Belts	T-9
11	Double-Sided Timing Belt	T-10
12	Timing Belt Stock	T-10
13	Example of Timing Belt Stock Use	T-10
14	Belt Construction	T-10
15	Belt Cross Section	T-12
16	Cord Twist	T-12
17	Right-Hand Rule Applicable to “S” Twist	T-13
18	“S” and “Z” Cord Lay of the Mold	T-13
19	Belt Tooth Configuration	T-15
20	Force/Deflection Method	T-52
21	Shaft Separation Method	T-52
22	Single Tension Vector Force	T-52
23	Idler Forces	T-53
24	Sonic Tension Meter	T-53
25	Angular Misalignment	T-53
26	Parallel Misalignment	T-54
27	Cartesian Coordinate System	T-57
28	Example of 5-Point Drive System	T-58
29	Belt Pull Vector Diagram	T-59
30	Vector Sum Correction Factor	T-60
31	Overhung Pulley	T-60
32	Pulley Between Bearings	T-60
33	Length Measuring Fixture	T-61
34	Typical Pulley Groove Tolerance Band	T-64
35	Expressions Used in Flange and Pulley Design	T-67
36	Terms Used for Timing Pulley Flange Design	T-68
37	Twin Power Belt Tolerances	T-69
38	Twin Power Belt Application	T-69
39	Belt Nomenclature	T-73
40	Belt Geometry	T-79
41	GT2 Belt Selection Guide	T-147
42	HTD Belt Selection Guide	T-148
43	Trapezoidal Belt Selection Guide	T-149