





■ 20° PRESSURE ANGLE

■ HUBLESS

■ 4 mm FACE WIDTH





MATERIAL: Brass

Catalog Number	No. of Teeth	P.D.	D	d Bore +0.025
A 1B 1MY04008	8	3.2	4	1.5
A 1B 1MY04010	10	4	4.8	2
A 1B 1MY04012	12	4.8	5.6	3
A 1B 1MY04014	14	5.6	6.4	3
A 1B 1MY04016	16	6.4	7.2	3
A 1B 1MY04018	18	7.2	8	3
A 1B 1MY04024	24	9.6	10.4	3



■ UNDERSIZED DIAMETER



MATERIAL: 303 Stainless Steel

Catalog Number	D Dia. +0.025	D <sub>1</sub> Dia. -0.004 -0.012	L Length ± 0.25
A 7X 1MP0550A	1.5	5	50
A 7X 1MP0550B	2	5	50
A 7X 1MP0675	3	6	75

Discounts available for large quantity orders.





# METRIC

## Pinions - Module 0.5

■ 20° PRESSURE ANGLE

■ HUBLESS

■ 4 mm FACE WIDTH



MATERIAL: Brass



Catalog Number	No. of Teeth	P.D.	D	d Bore +0.025
A 1B 1MY05006	6	3	4	1.5
A 1B 1MY05008	8	4	5	2
A 1B 1MY05010	10	5	6	
A 1B 1MY05012	12	6	7	
A 1B 1MY05014	14	7	8	3
A 1B 1MY05016	16	8	9	
A 1B 1MY05018	18	9	10	



# METRIC

## Pinion Shafts

■ UNDERSIZED DIAMETER



MATERIAL: 303 Stainless Steel

Catalog Number	D Dia. +0.025	D <sub>1</sub> Dia. -0.004 -0.012	L Length ± 0.25
A 7X 1MP0550A	1.5	5	50
A 7X 1MP0550B	2	5	50
A 7X 1MP0675	3	6	75

Discounts available for large quantity orders.




# METRIC

## Pinions - Module 0.8

■ 20° PRESSURE ANGLE

■ HUBLESS

■ 4 mm FACE WIDTH



1 GEARS

MATERIAL: Brass



Catalog Number	No. of Teeth	P.D.	D	d Bore +0.025
A 1B 1MY08006	6	4.8	6.4	3
A 1B 1MY08008	8	6.4	8	
A 1B 1MY08010	10	8	9.6	
A 1B 1MY08012	12	9.6	11.2	
A 1B 1MY08014	14	11.2	12.8	
A 1B 1MY08016	16	12.8	14.4	
A 1B 1MY08018	18	14.4	16	



# METRIC

## Pinion Shafts

■ UNDERSIZED DIAMETER



MATERIAL: 303 Stainless Steel

Catalog Number	D Dia. +0.025	D <sub>1</sub> Dia. -0.004 -0.012	L Length ± 0.25
A 7X 1MP0550B	2	5	50
A 7X 1MP0675	3	6	75

Discounts available for large quantity orders.