





20° PRESSURE ANGLE

1

GEARS



MATERIAL: Steel

Catalog Number	Module	No. of Teeth	P.D.	D	D ₁ Shank Diameter	L Minimum Usable Length				
A 1C29MY04025	0.4	25	10	10.8	6	80				
A 1C29MY04030		30	12	12.8						
A 1C29MY04032		32	12.8	13.6						
A 1C29MY04035		35	14	14.8						
A 1C29MY04036		80	36	14.4	15.2	6	80			
A 1C29MY04045			45	18	18.8					
A 1C29MY04048			48	19.2	20					
A 1C29MY04050			50	20	20.8					
A 1C29MY04060			150	60	24			24.8	12	80
A 1C29MY04064				64	25.6			26.4		
A 1C29MY04065				65	26			26.8		
A 1C29MY04070				70	28			28.8		
A 1C29MY04072		150	72	28.8	29.6	12	150			
A 1C29MY04075			75	30	30.8					
A 1C29MY04080			80	32	32.8					
A 1C29MY04085			85	34	34.8					
A 1C29MY04090			90	36	36.8					
A 1C29MY04095			95	38	38.8					
A 1C29MY04096			96	38.4	39.2					
A 1C29MY04100			100	40	40.8					
A 1C29MY04108	108	43.2	44							
A 1C29MY04120	120	48	48.8	12	80					
A 1C29MY05016	16	8	9							
A 1C29MY05018	18	9	10							
A 1C29MY05024	24	12	13							
A 1C29MY05028	28	14	15	6	80					
A 1C29MY05030	30	15	16							
A 1C29MY05032	32	16	17							
A 1C29MY05036	36	18	19							
A 1C29MY05040	40	20	21	12	80					
A 1C29MY05048	48	24	25							
A 1C29MY05050	50	25	26							
A 1C29MY05055	55	27.5	28							
A 1C29MY05056	56	28	29	6	80					
A 1C29MY05060	60	30	31							
A 1C29MY05065	65	32.5	33							
A 1C29MY05070	70	35	36							
A 1C29MY05072	72	36	37	12	150					
A 1C29MY05075	75	37.5	38							
A 1C29MY05080	80	40	41							
A 1C29MY05090	90	45	46							
A 1C29MY05096	96	48	49	12	200					
A 1C29MY05100	100	50	51							
A 1C29MY05110	110	55	56							
A 1C29MY05120	120	60	61							

