

TABLE OF CONTENTS	PAGE
SECTION 1 INTRODUCTION TO METRIC GEARS	T-7
1.1 Comparison Of Metric Gears With American Inch Gears.....	T-8
1.1.1 Comparison of Basic Racks	T-8
1.1.2 Metric ISO Basic Rack.....	T-8
1.1.3 Comparison of Gear Calculation Equations.....	T-9
1.2 Metric Standards Worldwide.....	T-9
1.2.1 ISO Standards.....	T-9
1.2.2 Foreign Metric Standards.....	T-9
1.3 Japanese Metric Standards In This Text.....	T-9
1.3.1 Application of JIS Standards.....	T-9
1.3.2 Symbols	T-13
1.3.3 Terminology.....	T-16
1.3.4 Conversion	T-16
SECTION 2 INTRODUCTION TO GEAR TECHNOLOGY	T-17
2.1 Basic Geometry Of Spur Gears.....	T-17
2.2 The Law Of Gearing	T-19
2.3 The Involute Curve.....	T-19
2.4 Pitch Circles.....	T-20
2.5 Pitch And Module	T-20
2.6 Module Sizes And Standards.....	T-21
2.7 Gear Types And Axial Arrangements.....	T-26
2.7.1 Parallel Axes Gears	T-26
2.7.2 Intersecting Axes Gears	T-28
2.7.3 Nonparallel and Nonintersecting Axes Gears	T-28
2.7.4 Other Special Gears	T-29
SECTION 3 DETAILS OF INVOLUTE GEARING	T-30
3.1 Pressure Angle.....	T-30
3.2 Proper Meshing And Contact Ratio	T-30
3.2.1 Contact Ratio	T-32
3.3 The Involute Function.....	T-32
SECTION 4 SPUR GEAR CALCULATIONS	T-34
4.1 Standard Spur Gear.....	T-34
4.2 The Generating Of A Spur Gear.....	T-35
4.3 Undercutting	T-36
4.4 Enlarged Pinions	T-37
4.5 Profile Shifting	T-37
4.6 Profile Shifted Spur Gear.....	T-39
4.7 Rack And Spur Gear	T-41

TABLE OF CONTENTS

PAGE

SECTION 5 INTERNAL GEARS	T-42
5.1 Internal Gear Calculations.....	T-42
5.2 Interference In Internal Gears.....	T-44
5.3 Internal Gear With Small Differences In Numbers Of Teeth.....	T-46
SECTION 6 HELICAL GEARS	T-47
6.1 Generation Of The Helical Tooth.....	T-48
6.2 Fundamentals Of Helical Teeth	T-48
6.3 Equivalent Spur Gear.....	T-50
6.4 Helical Gear Pressure Angle.....	T-51
6.5 Importance Of Normal Plane Geometry.....	T-51
6.6 Helical Tooth Proportions	T-51
6.7 Parallel Shaft Helical Gear Meshes.....	T-51
6.8 Helical Gear Contact Ratio	T-52
6.9 Design Considerations	T-52
6.9.1 Involute Interference.....	T-52
6.9.2 Normal vs. Radial Module (Pitch).....	T-52
6.10 Helical Gear Calculations	T-53
6.10.1 Normal System Helical Gear.....	T-53
6.10.2 Radial System Helical Gear	T-54
6.10.3 Sunderland Double Helical Gear	T-55
6.10.4 Helical Rack	T-56
SECTION 7 SCREW GEAR OR CROSSED HELICAL GEAR MESHES	T-57
7.1 Features	T-57
7.1.1 Helix Angle and Hands.....	T-57
7.1.2 Module.....	T-57
7.1.3 Center Distance.....	T-58
7.1.4 Velocity Ratio	T-58
7.2 Screw Gear Calculations	T-58
7.3 Axial Thrust Of Helical Gears.....	T-60
SECTION 8 BEVEL GEARING	T-60
8.1 Development And Geometry Of Bevel Gears	T-61
8.2 Bevel Gear Tooth Proportions.....	T-62
8.3 Velocity Ratio	T-62
8.4 Forms Of Bevel Teeth.....	T-62
8.5 Bevel Gear Calculations	T-64
8.5.1 Gleason Straight Bevel Gears.....	T-66
8.5.2 Standard Straight Bevel Gears.....	T-68
8.5.3 Gleason Spiral Bevel Gears	T-69
8.5.4 Gleason Zerol Spiral Bevel Gears	T-70

TABLE OF CONTENTS	PAGE
SECTION 9 WORM MESH	T-72
9.1 Worm Mesh Geometry	T-72
9.1.1 Worm Tooth Proportions	T-72
9.1.2 Number of Threads	T-72
9.1.3 Pitch Diameters, Lead and Lead Angle	T-73
9.1.4 Center Distance	T-73
9.2 Cylindrical Worm Gear Calculations	T-73
9.2.1 Axial Module Worm Gears	T-75
9.2.2 Normal Module System Worm Gears	T-76
9.3 Crowning Of The Worm Gear Tooth	T-77
9.4 Self-Locking Of Worm Mesh	T-80
SECTION 10 TOOTH THICKNESS	T-81
10.1 Chordal Thickness Measurement	T-81
10.1.1 Spur Gears	T-81
10.1.2 Spur Racks and Helical Racks	T-81
10.1.3 Helical Gears	T-82
10.1.4 Bevel Gears	T-82
10.1.5 Worms and Worm Gears	T-84
10.2 Span Measurement Of Teeth	T-86
10.2.1 Spur and Internal Gears	T-86
10.2.2 Helical Gears	T-87
10.3 Over Pins (Balls) Measurement	T-88
10.3.1 Spur Gears	T-89
10.3.2 Spur Racks and Helical Racks	T-91
10.3.3 Internal Gears	T-92
10.3.4 Helical Gears	T-94
10.3.5 Three Wire Method of Worm Measurement	T-96
10.4 Over Pins Measurements For Fine Pitch Gears With Specific Numbers Of Teeth	T-98
SECTION 11 CONTACT RATIO	T-108
11.1 Radial Contact Ratio Of Spur And Helical Gears, ϵ_{α}	T-108
11.2 Contact Ratio Of Bevel Gears, ϵ_{α}	T-109
11.3 Contact Ratio For Nonparallel And Nonintersecting Axes Pairs, ϵ	T-110
11.4 Axial (Overlap) Contact Ratio, ϵ_{β}	T-110
SECTION 12 GEAR TOOTH MODIFICATIONS	T-111
12.1 Tooth Tip Relief	T-111
12.2 Crowning And Side Relieving	T-112
12.3 Topping And Semitopping	T-112

TABLE OF CONTENTS

PAGE

SECTION 13 GEAR TRAINS	T-113
13.1 Single-Stage Gear Train.....	T-113
13.1.1 Types of Single-Stage Gear Trains.....	T-113
13.2 Two-Stage Gear Train.....	T-114
13.3 Planetary Gear System	T-115
13.3.1 Relationship Among the Gears in a Planetary Gear System	T-116
13.3.2 Speed Ratio of Planetary Gear System	T-117
13.4 Constrained Gear System.....	T-118
SECTION 14 BACKLASH	T-119
14.1 Definition Of Backlash.....	T-120
14.2 Backlash Relationships.....	T-123
14.2.1 Backlash of a Spur Gear Mesh.....	T-123
14.2.2 Backlash of Helical Gear Mesh.....	T-124
14.2.3 Backlash of Straight Bevel Gear Mesh.....	T-125
14.2.4 Backlash of a Spiral Bevel Gear Mesh	T-125
14.2.5 Backlash of Worm Gear Mesh.....	T-126
14.3 Tooth Thickness And Backlash.....	T-126
14.4 Gear Train And Backlash	T-127
14.5 Methods Of Controlling Backlash	T-128
14.5.1 Static Method	T-128
14.5.2 Dynamic Methods.....	T-129
SECTION 15 GEAR ACCURACY	T-131
15.1 Accuracy Of Spur And Helical Gears	T-131
15.1.1 Pitch Errors of Gear Teeth	T-131
15.1.2 Tooth Profile Error, f_f	T-133
15.1.3 Runout Error of Gear Teeth, F_r	T-133
15.1.4 Lead Error, f_{β}	T-133
15.1.5 Outside Diameter Runout and Lateral Runout.....	T-135
15.2 Accuracy Of Bevel Gears	T-135
15.3 Running (Dynamic) Gear Testing	T-137
SECTION 16 GEAR FORCES	T-138
16.1 Forces In A Spur Gear Mesh.....	T-139
16.2 Forces In A Helical Gear Mesh.....	T-139
16.3 Forces In A Straight Bevel Gear Mesh.....	T-140
16.4 Forces In A Spiral Bevel Gear Mesh	T-142
16.4.1 Tooth Forces on a Convex Side Profile.....	T-142
16.4.2 Tooth Forces on a Concave Side Profile	T-143
16.5 Forces In A Worm Gear Mesh	T-146
16.5.1 Worm as the Driver.....	T-146
16.5.2 Worm Gear as the Driver	T-148
16.6 Forces In A Screw Gear Mesh	T-148

TABLE OF CONTENTS

PAGE

SECTION 17 STRENGTH AND DURABILITY OF GEARS	T-150
17.1 Bending Strength Of Spur And Helical Gears	T-150
17.1.1 Determination of Factors in the Bending Strength Equation.....	T-151
17.1.2 Tooth Profile Factor, Y_F	T-151
17.1.3 Load Distribution Factor, Y_ϵ	T-151
17.1.4 Helix Angle Factor, Y_β	T-153
17.1.5 Life Factor, K_L	T-154
17.1.6 Dimension Factor of Root Stress, K_{FX}	T-154
17.1.7 Dynamic Load Factor, K_V	T-154
17.1.8 Overload Factor, K_O	T-155
17.1.9 Safety Factor of Bending Failure, S_F	T-155
17.1.10 Allowable Bending Stress at Root, $\sigma_{F\ lim}$	T-155
17.1.11 Example of Bending Strength Calculation	T-159
17.2 Surface Strength Of Spur And Helical Gears.....	T-160
17.2.1 Conversion Formulas.....	T-160
17.2.2 Surface Strength Equations	T-160
17.2.3 Determination of Factors in the Surface Strength Equations.....	T-160
17.2.4 Contact Ratio Factor, Z_ϵ	T-162
17.2.5 Helix Angle Factor, Z_β	T-163
17.2.6 Life Factor, K_{HL}	T-163
17.2.7 Lubricant Factor, Z_L	T-163
17.2.8 Surface Roughness Factor, Z_R	T-163
17.2.9 Sliding Speed Factor, Z_V	T-164
17.2.10 Hardness Ratio Factor, Z_W	T-164
17.2.11 Dimension Factor, K_{HX}	T-164
17.2.12 Tooth Flank Load Distribution Factor, $K_{H\beta}$	T-164
17.2.13 Dynamic Load Factor, K_V	T-165
17.2.14 Overload Factor, K_O	T-165
17.2.15 Safety Factor for Pitting, S_H	T-165
17.2.16 Allowable Hertz Stress, $\sigma_{H\ lim}$	T-165
17.2.17 Example of Surface Stress Calculation.....	T-170
17.3 Bending Strength Of Bevel Gears	T-171
17.3.1 Conversion Formulas.....	T-171
17.3.2 Bending Strength Equations	T-172
17.3.3 Determination of Factors in Bending Strength Equations.....	T-172
17.3.4 Examples of Bevel Gear Bending Strength Calculations	T-179
17.4 Surface Strength Of Bevel Gears	T-180
17.4.1 Basic Conversion Formulas.....	T-180
17.4.2 Surface Strength Equations	T-180
17.4.3 Determination of Factors in Surface Strength Equations	T-181
17.4.4 Examples of Bevel Gear Surface Strength Calculations.....	T-184
17.5 Strength Of Worm Gearing	T-185
17.5.1 Basic Formulas.....	T-185
17.5.2 Torque, Tangential Force and Efficiency.....	T-186
17.5.3 Friction Coefficient, μ	T-186
17.5.4 Surface Strength of Worm Gearing Mesh	T-187
17.5.5 Determination of Factors in Worm Gear Surface Strength Equations.....	T-188
17.5.6 Examples of Worm Mesh Strength Calculation	T-193

TABLE OF CONTENTS

PAGE

SECTION 18 DESIGN OF PLASTIC GEARS	T-194
18.1 General Considerations Of Plastic Gearing	T-194
18.2 Properties Of Plastic Gear Materials	T-194
18.3 Choice Of Pressure Angles And Modules	T-204
18.4 Strength Of Plastic Spur Gears	T-204
18.4.1 Bending Strength of Spur Gears	T-205
18.4.2 Surface Strength of Plastic Spur Gears	T-206
18.4.3 Bending Strength of Plastic Bevel Gears	T-206
18.4.4 Bending Strength of Plastic Worm Gears	T-209
18.4.5 Strength of Plastic Keyway	T-210
18.5 Effect Of Part Shrinkage On Plastic Gear Design	T-210
18.6 Proper Use Of Plastic Gears	T-212
18.6.1 Backlash	T-212
18.6.2 Environment and Tolerances	T-213
18.6.3 Avoiding Stress Concentration	T-213
18.6.4 Metal Inserts	T-213
18.6.5 Attachment of Plastic Gears to Shafts	T-214
18.6.6 Lubrication	T-214
18.6.7 Molded vs. Cut Plastic Gears	T-215
18.6.8 Elimination of Gear Noise	T-215
18.7 Mold Construction	T-216
SECTION 19 FEATURES OF TOOTH SURFACE CONTACT	T-221
19.1 Surface Contact Of Spur And Helical Meshes	T-221
19.2 Surface Contact Of A Bevel Gear	T-221
19.2.1 The Offset Error of Shaft Alignment	T-222
19.2.2 The Shaft Angle Error of Gear Box	T-222
19.2.3 Mounting Distance Error	T-222
19.3 Surface Contact Of Worm And Worm Gear	T-223
19.3.1 Shaft Angle Error	T-223
19.3.2 Center Distance Error	T-224
19.3.3 Mounting Distance Error	T-224
SECTION 20 LUBRICATION OF GEARS	T-225
20.1 Methods Of Lubrication	T-225
20.1.1 Grease Lubrication	T-225
20.1.2 Splash Lubrication	T-226
20.1.3 Forced-Circulation Lubrication	T-227
20.2 Gear Lubricants	T-227
20.2.1 Viscosity of Lubricant	T-227
20.2.2 Selection of Lubricant	T-229
SECTION 21 GEAR NOISE	T-231
REFERENCES AND LITERATURE OF GENERAL INTEREST	T-232