

ADJUSTABLE
NONMARRING

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

➤ **MATERIAL:**



303 Stainless Steel

➤ **SPECIFICATIONS:**

- d₁, d₂ Tolerance:
2.5 & 3 mm +0.01/0
- 4, 5 & 6 mm +0.012/0
- 8 & 10 mm +0.015/0
- 12 mm +0.018/0

d₁ and d₂ bores concentric to within 0.025 mm T.I.R.
Fairloc® hubs require controlled shaft tolerances.
Suggested tolerance according to g6, h6 or h7.

Other sizes and material available on special order.



METRIC COMPONENT

Catalog Number	d ₁ Bore H7	d ₂ Bore H7	D ₁ Dia.	D ₂ Dia.	L	l ₁	l ₂	T ₁	T ₂	Max. Clear. Radius	Max. Torque N • m
S51FCZM025030	2.5	3	11	11	19	—	9	M2	M2	6.4	0.4
S51FCZM025040	2.5	4	11	14	19	8	9	M2	M2.5	8.3	0.4
S51FCZM025050	2.5	5	11	14	19	8	9	M2	M2.5	8.3	0.4
S51FCZM030030	3	3	11	11	19	—	—	M2	M2	6.4	0.45
S51FCZM030040	3	4	11	14	19	8	9	M2	M2.5	8.3	0.45
S51FCZM030050	3	5	11	14	19	8	9	M2	M2.5	8.3	0.45
S51FCZM030060	3	6	11	17	21	8	11	M2	M3	11.3	0.45
S51FCZM040040	4	4	14	14	19	—	—	M2.5	M2.5	8.3	0.57
S51FCZM040050	4	5	14	14	19	—	9	M2.5	M2.5	8.3	0.57
S51FCZM040060	4	6	14	17	21	8	11	M2.5	M3	11.3	0.57
S51FCZM040080	4	8	14	17	21	8	11	M2.5	M3	11.3	0.57
S51FCZM050050	5	5	14	14	19	—	—	M2.5	M2.5	8.3	0.9
S51FCZM050060	5	6	14	17	21	8	11	M2.5	M3	11.3	0.9
S51FCZM050080	5	8	14	17	21	8	11	M2.5	M3	11.3	0.9
S51FCZM050100	5	10	14	24	25	8	15	M2.5	M4	14	0.9
S51FCZM060060	6	6	17	17	23	—	—	M3	M3	11.3	1.3
S51FCZM060080	6	8	17	17	23	—	12	M3	M3	11.3	1.3
S51FCZM060100	6	10	17	24	27	10	15	M3	M4	14	1.3
S51FCZM060120	6	12	17	26	30	10	18	M3	M4	15.1	1.3
S51FCZM080080	8	8	17	17	23	—	—	M3	M3	11.3	2.6
S51FCZM080100	8	10	17	24	27	10	15	M3	M4	14	2.6
S51FCZM080120	8	12	17	26	30	10	18	M3	M4	15.1	2.6
S51FCZM100100	10	10	24	24	35	—	—	M4	M4	14	3.5
S51FCZM100120	10	12	24	26	35	14	18	M4	M4	15.1	3.5
S51FCZM120120	12	12	26	26	38	—	—	M4	M4	15.1	5.1

