


GROUND RACKS – MODULE 0.5, 0.8, 1 & 1.5

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

ISO CLASS 5
GROUND TEETH
20° PRESSURE ANGLE




> MATERIAL:

AISI 1045 Steel Hardened
to HRC 27...32

> SPECIFICATIONS:

Tolerance h8: 8 & 10 mm 0/-0.022
12 & 15 mm 0/-0.027
20 mm 0/-0.033



METRIC COMPONENT

Catalog Number	Module	No. of Usable Teeth	S Face Width h8	H Height h8	H ₀ Pitch Distance	L Stock Length mm
S18C05M128P0812G	0.5	128	8	12	11.5	201.06
S18C08M080P0812G	0.8	80	8	12	11.2	201.06
S18C10M096P1015G	1	96	10	15	14	301.59
S18C15M064P1520G	1.5	64	15	20	18.5	301.59

See index for ground spur gears.

JOINING GAUGES for GROUND RACKS – MODULE 0.5, 0.8 1 & 1.5

ISO CLASS 5
GROUND TEETH
20° PRESSURE ANGLE




> MATERIAL:

AISI 1045 Steel Hardened
to HRC 27...32

> SPECIFICATIONS:

Tolerance h8: 8 & 10 mm 0/-0.022
12 & 15 mm 0/-0.027
20 mm 0/-0.033



METRIC COMPONENT

Catalog Number	Mod.	1/2 Module		No. of Teeth	S Face Width h8	H Height h8	H ₀ Pitch Distance	L Stock Length approx.
		Dim.	Tol.					
S18C05MGAGE-G	0.5	0.785	-0.02 / -0.08	29	8	12	11.5	45.3
S18C08MGAGE-G	0.8	1.256	-0.03 / -0.12	18	8	12	11.2	44.9
S18C10MGAGE-G	1	1.57	-0.03 / -0.12	14	10	15	14	43.6
S18C15MGAGE-G	1.5	2.356	-0.04 / -0.16	9	15	20	18.5	41.9

See index for ground spur gears.

ISO CLASS 8

MODULE 0.3, 0.5, 0.75, 0.8 & 1

20° PRESSURE ANGLE


PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM



QUALITY CLASS

> MATERIAL:

Brass, Stainless Steel or Steel





METRIC COMPONENT

Catalog Number	Module	Material	S Face Width	H Height	P Pitch Height	L Length mm
A 1B12MYK03200	0.3	Brass	3	8	7.7	200
A 1B12MYK05200	0.5	Brass	3	8	7.5	200
A 1B12MYKW05200	0.5	Brass	8	8	7.5	200
A 1B12MYK05500	0.5	Brass	8	10	9.5	505
A 1X12MYK05200	0.5	Stainless Steel	3	10	9.5	200
A 1X12MYK05300	0.5	Stainless Steel	4.8	9.5	9	300
A 1X12MYKW05200	0.5	Stainless Steel	8	8	7.5	200
A 1X12MYK05500	0.5	Stainless Steel	8	10	9.5	505
A 1B12MYKH7200	0.75	Brass	3	8	7.25	200
A 1B12MYKH7500	0.75	Brass	3	10	9.25	505
A 1B12MYKWH7200	0.75	Brass	8	8	7.25	200
A 1B12MYKWH7500	0.75	Brass	8	10	9.25	505
A 1X12MYKH7200	0.75	Stainless Steel	3	10	9.25	200
A 1X12MYKWH7200	0.75	Stainless Steel	8	8	7.25	200
A 1X12MYKH7500	0.75	Stainless Steel	8	10	9.25	505
A 1B12MYK08500	0.8	Brass	5	10	9.2	505
A 1B12MYK08200	0.8	Brass	7	7	6.2	200
A 1B12MYKW08500	0.8	Brass	7	10	9.2	505
A 1X12MYK08500	0.8	Stainless Steel	5	10	9.2	505
A 1X12MYK08200	0.8	Stainless Steel	7	7	6.2	200
A 1X12MYKW08500	0.8	Stainless Steel	7	10	9.2	505
A 1C12MYK10300	1	Steel	10	10	9	300
A 1C12MYK10500	1	Steel	10	10	9	500
A 1C12MYK101000	1	Steel	10	15	14	1021
A 1X12MYK10500	1	Stainless Steel	8	10	9	500
A 1X12MYK10300	1	Stainless Steel	10	10	9	300
A 1X12MYKW10500	1	Stainless Steel	10	10	9	500

ISO CLASS 8
20° PRESSURE ANGLE

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM


› **MATERIAL:**
Steel, Brass, or Nylon



METRIC COMPONENT

Catalog Number	Module	Material	S Face Width	H Height mm	P Pitch Height	L Length mm
A 1C12MY04A075	0.4	Steel	4.8	9.5	9.13	75
A 1C12MY04A150	0.4	Steel	4.8	9.5	9.13	150
A 1C12MY04A300	0.4	Steel	4.8	9.5	9.13	300
A 1B12MY04A075	0.4	Brass	4.8	9.5	9.13	75
A 1B12MY04A150	0.4	Brass	4.8	9.5	9.13	150
A 1B12MY04A300	0.4	Brass	4.8	9.5	9.13	300
A 1C12MY04B075	0.4	Steel	4.8	4.8	4.34	75
A 1C12MY04B150	0.4	Steel	4.8	4.8	4.34	150
A 1C12MY04B300	0.4	Steel	4.8	4.8	4.34	300
A 1B12MY04B075	0.4	Brass	4.8	4.8	4.34	75
A 1B12MY04B150	0.4	Brass	4.8	4.8	4.34	150
A 1B12MY04B300	0.4	Brass	4.8	4.8	4.34	300
A 1P12MY04C075	0.4	Nylon	6.3	6.3	5.94	75
A 1P12MY04C150	0.4	Nylon	6.3	6.3	5.94	150
A 1P12MY04C300	0.4	Nylon	6.3	6.3	5.94	300
A 1C12MY05A075	0.5	Steel	4.8	9.5	9.03	75
A 1C12MY05A150	0.5	Steel	4.8	9.5	9.03	150
A 1C12MY05A300	0.5	Steel	4.8	9.5	9.03	300
A 1B12MY05A075	0.5	Brass	4.8	9.5	9.03	75
A 1B12MY05A150	0.5	Brass	4.8	9.5	9.03	150
A 1B12MY05A300	0.5	Brass	4.8	9.5	9.03	300
A 1C12MY05B075	0.5	Steel	4.8	4.8	4.26	75
A 1C12MY05B150	0.5	Steel	4.8	4.8	4.26	150
A 1C12MY05B300	0.5	Steel	4.8	4.8	4.26	300
A 1B12MY05B075	0.5	Brass	4.8	4.8	4.26	75
A 1B12MY05B150	0.5	Brass	4.8	4.8	4.26	150
A 1B12MY05B300	0.5	Brass	4.8	4.8	4.26	300
A 1P12MY05C075	0.5	Nylon	6.3	6.3	5.85	75
A 1P12MY05C150	0.5	Nylon	6.3	6.3	5.85	150
A 1P12MY05C300	0.5	Nylon	6.3	6.3	5.85	300



Continued on the next page



ISO CLASS 8
20° PRESSURE ANGLE

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

› **MATERIAL:**
Steel, Brass, or Nylon



METRIC COMPONENT

Catalog Number	Module	Material	S Face Width	H Height	P Pitch Height	L Length mm
A 1C12MY08A075	0.8	Steel	6.3	12.7	11.9	75
A 1C12MY08A150	0.8	Steel	6.3	12.7	11.9	150
A 1C12MY08A300	0.8	Steel	6.3	12.7	11.9	300
A 1B12MY08A075	0.8	Brass	6.3	12.7	11.9	75
A 1B12MY08A150	0.8	Brass	6.3	12.7	11.9	150
A 1B12MY08A300	0.8	Brass	6.3	12.7	11.9	300
A 1C12MY08B075	0.8	Steel	6.3	6.3	5.56	75
A 1C12MY08B150	0.8	Steel	6.3	6.3	5.56	150
A 1C12MY08B300	0.8	Steel	6.3	6.3	5.56	300
A 1B12MY08B075	0.8	Brass	6.3	6.3	5.56	75
A 1B12MY08B150	0.8	Brass	6.3	6.3	5.56	150
A 1B12MY08B300	0.8	Brass	6.3	6.3	5.56	300
A 1P12MY08B075	0.8	Nylon	6.3	6.3	5.56	75
A 1P12MY08B150	0.8	Nylon	6.3	6.3	5.56	150
A 1P12MY08B300	0.8	Nylon	6.3	6.3	5.56	300
A 1C12MY10B150	1	Steel	7.9	15.9	14.88	150
A 1C12MY10B300	1	Steel	7.9	15.9	14.88	300
A 1C12MY10B600	1	Steel	7.9	15.9	14.88	600
A 1B12MY10B150	1	Brass	7.9	15.9	14.88	150
A 1B12MY10B300	1	Brass	7.9	15.9	14.88	300
A 1B12MY10B600	1	Brass	7.9	15.9	14.88	600
A 1C12MY10C150	1	Steel	7.9	7.9	6.94	150
A 1C12MY10C300	1	Steel	7.9	7.9	6.94	300
A 1C12MY10C600	1	Steel	7.9	7.9	6.94	600
A 1B12MY10C150	1	Brass	7.9	7.9	6.94	150
A 1B12MY10C300	1	Brass	7.9	7.9	6.94	300
A 1B12MY10C600	1	Brass	7.9	7.9	6.94	600
A 1P12MY10A150	1	Nylon	9.5	9.5	8.53	150
A 1P12MY10A300	1	Nylon	9.5	9.5	8.53	300
A 1P12MY10A600	1	Nylon	9.5	9.5	8.53	600

Continued from the previous page

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16

I

RACKS • MODULE 1.5 TO 3**SDP/SI**

R

ISO CLASS 8
 MODULE 1.5, 2, 2.5 & 3
 20° PRESSURE ANGLE

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

T

► **MATERIAL:**
 Steel




0 10

QUALITY CLASS

1

2

3



4

METRIC COMPONENT

5

Catalog Number	Module	S Face Width	H Height	P Pitch Height	L Length mm
A 1C12MYK15300	1.5	16	16	14.5	300
A 1C12MYKW15500	1.5	16	16	14.5	500
A 1C12MYK151000	1.5	16	16	14.5	1008.5
A 1C12MYK15500	1.5	12	16	14.5	500
A 1C12MYK20300	2	20	20	18	300
A 1C12MYK20500	2	20	20	18	500
A 1C12MYKW201000	2	20	20	18	1005.3
A 1C12MYK201000	2	14	20	18	1005.3
A 1C12MYK25300	2.5	25	25	22.5	300
A 1C12MYK25500	2.5	25	25	22.5	500
A 1C12MYKW251000	2.5	25	25	22.5	1005.3
A 1C12MYK251000	2.5	18	25	22.5	1005.3
A 1C12MYK30300	3	30	30	27	300
A 1C12MYK30500	3	30	30	27	500
A 1C12MYKW301000	3	30	30	27	1008.5
A 1C12MYK301000	3	22	30	27	1008.5

6

7

8

9

10

11

12

13

14

15


A

ROUND RACKS – MODULE 0.5 TO 1

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

ISO CLASS 9
20° PRESSURE ANGLE

> **MATERIAL:**
304 Stainless Steel




METRIC COMPONENT

Catalog Number	Module	D h7 (0 -0.015)	P Pitch Height	l	l ₂ Ref.	l ₃	L Length mm ± 1
S181YYM0508200	0.5	8	7.5	149	53	10.7	202
S181YYM0758200	0.75		7.25	148	54	13	
S181YYM0808200	0.8		7.2			13.4	
S181YYM100A300	1	10	9	238	67	15	305

NONMETALLIC RACKS - MODULE 0.4 TO 3.0

20° PRESSURE ANGLE

> **MATERIAL:**
Molded Acetal
Machined Cast Nylon




METRIC COMPONENT

Catalog Number	Module	Material	S Face Width	H Height	P Pitch Height	L Length mm	
A 1M12MYP0425	0.4	Acetal (Molded)	3	3.9	3.5	250	
A 1M12MYZ0525	0.5		4	4.5	4		
A 1M12MYZ0525A			4	6	5.5		
A 1M12MYZ0725	0.7		6	6.7	6		
A 1M12MYP0825	0.8		5	7.3	6.5		
A 1M12MYZ1025	1		9	9	8		
A 1M12MYZ1225	1.25		10	11	9.75		
A 1M12MYZ1525	1.5		12	12	10.5		
A 1M12MYZ2025	2		15.4	11	9		
A 1M12MYZ3025	3		19.4	15	12		
A 1M12MYH100500	1		10	12	11		505
A 1M12MYH150500	1.5		15	20	18.5		
A 1M12MYH151000		1010					
A 1M12MYH200500	2	Nylon (Machined)	20	25	23	505	
A 1M12MYH201000			1010				
A 1M12MYH250500	2.5		25	30	27.5	505	
A 1M12MYH251000						1010	
A 1M12MYH300500	3		30	35	32	505	
A 1M12MYH301000						1010	

GROUND RACKS – CP 2 & 5


PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

ISO CLASS 5
GROUND TEETH
20° PRESSURE ANGLE



> MATERIAL:
AISI 1045 Steel Hardened
to HRC 27...32

> SPECIFICATIONS:
Tolerance h8: 8 mm 0/-0.022
12 & 15 mm 0/-0.027
20 mm 0/-0.033



METRIC COMPONENT

Catalog Number	Circular Pitch	No. of Usable Teeth	S Face Width h8	H Height h8	H ₀ Pitch Distance	L Stock Length mm
S18CCPM020P100G	2	100	8	12	11.364	200
S18CCPM050P060G	5	60	15	20	18.409	300

See index for ground circular pitch spur gears.


JOINING GAUGE for CP GROUND RACKS – CP 2 & 5

ISO CLASS 5
GROUND TEETH
20° PRESSURE ANGLE



> MATERIAL:
AISI 1045 Steel Hardened
to HRC 27...32

> SPECIFICATIONS:
Tolerance h8: 8 mm 0/-0.022
12 & 15 mm 0/-0.027
20 mm 0/-0.033



METRIC COMPONENT

Catalog Number	Circular Pitch	1/2 Module		No. of Teeth	S Face Width h8	H Height h8	H ₀ Pitch Distance	L Stock Length mm
		Dim.	Tol.					
S18CCPM020GAGE-G	2	1	-0.02 / -0.08	23	8	12	11.364	45.7
S18CCPM050GAGE-G	5	2.5	-0.04 / -0.16	8	15	20	18.409	39.4

See index for ground circular pitch spur gears.