


20° PRESSURE ANGLE

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

> MATERIAL:
Steel




METRIC COMPONENT

Catalog Number	No. of Teeth	P.D.	D Dia.	D ₁ Shank Dia.	L Minimum Usable Length
Module 0.4					
A 1C29MY04025	25	10	10.8	6	80
A 1C29MY04030	30	12	12.8	6	80
A 1C29MY04032	32	12.8	13.6	6	80
A 1C29MY04035	35	14	14.8	6	80
A 1C29MY04036	36	14.4	15.2	6	80
A 1C29MY04045	45	18	18.8	6	80
A 1C29MY04048	48	19.2	20	6	80
A 1C29MY04050	50	20	20.8	6	80
A 1C29MY04060	60	24	24.8	12	80
A 1C29MY04064	64	25.6	26.4	12	150
A 1C29MY04065	65	26	26.8	12	150
A 1C29MY04070	70	28	28.8	12	150
A 1C29MY04072	72	28.8	29.6	12	150
A 1C29MY04075	75	30	30.8	12	150
A 1C29MY04080	80	32	32.8	12	150
A 1C29MY04085	85	34	34.8	12	150
A 1C29MY04090	90	36	36.8	12	150
A 1C29MY04095	95	38	38.8	12	200
A 1C29MY04096	96	38.4	39.2	12	200
A 1C29MY04100	100	40	40.8	12	200
A 1C29MY04108	108	43.2	44	12	200
A 1C29MY04120	120	48	48.8	12	200
Module 0.5					
A 1C29MY05016	16	8	9	6	80
A 1C29MY05018	18	9	10	6	80
A 1C29MY05024	24	12	13	6	80
A 1C29MY05028	28	14	15	6	80
A 1C29MY05030	30	15	16	6	80
A 1C29MY05032	32	16	17	6	80
A 1C29MY05036	36	18	19	6	80
A 1C29MY05040	40	20	21	6	80
A 1C29MY05048	48	24	25	12	80
A 1C29MY05050	50	25	26	12	150
A 1C29MY05055	55	27.5	28.5	12	150
A 1C29MY05056	56	28	29	12	150
A 1C29MY05060	60	30	31	12	150
A 1C29MY05065	65	32.5	33.5	12	150
A 1C29MY05070	70	35	36	12	150
A 1C29MY05072	72	36	37	12	150
A 1C29MY05075	75	37.5	38.5	12	200
A 1C29MY05080	80	40	41	12	200
A 1C29MY05090	90	45	46	12	200
A 1C29MY05096	96	48	49	12	200
A 1C29MY05100	100	50	51	12	200
A 1C29MY05110	110	55	56	16	200
A 1C29MY05120	120	60	61	16	200

20° PRESSURE ANGLE

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

> MATERIAL:
Steel



METRIC COMPONENT

Catalog Number	No. of Teeth	P.D.	D Dia.	D ₁ Shank Dia.	L Minimum Usable Length
Module 0.8					
* A 1C29MY08012	12	9.6	11.2	6	80
* A 1C29MY08014	14	11.2	12.8	6	80
* A 1C29MY08016	16	12.8	14.4	6	80
* A 1C29MY08018	18	14.4	16	6	80
* A 1C29MY08024	24	19.2	20.8	6	80
* A 1C29MY08030	30	24	25.6	12	80
A 1C29MY08032	32	25.6	27.2	12	150
A 1C29MY08036	36	28.8	30.4	12	150
A 1C29MY08040	40	32	33.6	12	150
A 1C29MY08045	45	36	37.6	12	150
A 1C29MY08050	50	40	41.6	12	150
A 1C29MY08060	60	48	49.6	12	200
A 1C29MY08064	64	51.2	52.8	12	200
A 1C29MY08075	75	60	61.6	16	200
A 1C29MY08080	80	64	65.6	16	200
A 1C29MY08090	90	72	73.6	16	200
Module 1					
A 1C29MY10014	14	14	16	6	80
A 1C29MY10016	16	16	18	6	80
A 1C29MY10020	20	20	22	6	80
A 1C29MY10024	24	24	26	12	80
A 1C29MY10028	28	28	30	12	150
A 1C29MY10030	30	30	32	12	150
A 1C29MY10032	32	32	34	12	150
A 1C29MY10036	36	36	38	12	150
A 1C29MY10040	40	40	42	12	200
A 1C29MY10045	45	45	47	12	200
A 1C29MY10048	48	48	50	12	200
A 1C29MY10050	50	50	52	12	200
A 1C29MY10060	60	60	62	16	200
A 1C29MY10064	64	64	66	16	200
A 1C29MY10072	72	72	74	16	200

* Minimum usable length: 75 mm to 80 mm