

PROTECTS FRAGILE SUBJECTS FROM  
MICRO-VIBRATIONS AND LIGHT SHOCKS

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

**> MATERIAL:**

- Collar - Brass
- Bushing - Silicone Gel

More technical data is given  
on preceding pages.




Fig. 1





Fig. 2



INSTALLATION DIAGRAM




Fig. 3

**METRIC COMPONENT**

Catalog Number	Fig. No.	d Collar I.D.	L Collar Length	Collar Thickness	Optimum Load kgf/leg	Resonance Point Hz	Resonance Magnification dB	Recommended Frequency Hz
A10Z61MS	1	3	6	0.5	0.05 to 0.188	64 to 42	7 to 9	0.05 kg • 90 ~ 0.188 kg • 60 ~
A10Z61MA1	2	3	7	1	0.125 to 0.625	67 to 35	9 to 10	0.125 kg • 95 ~ 0.625 kg • 50 ~
A10Z61MA2					0.625 to 1	49 to 37	15 to 16	0.625 kg • 70 ~ 1 kg • 55 ~
A10Z61MB1	3	4	11	1	1 to 3.75	49 to 23	15 to 17	1 kg • 70 ~ 3.75 kg • 35 ~
A10Z61MB2					3.75 to 8	20 to 15	19 to 23	3.75 kg • 30 ~ 8 kg • 25 ~

I  
R  
T  
1  
2  
3  
4  
5  
6  
7  
8  
9  
10  
11  
12  
13  
14  
15  
A

# SILICONE GEL SHEETS

# SDP/SI


LOW RESONANCE MAGNIFICATION  
 OZONE, UV AND CHEMICAL RESISTANT  
 SHOCK ABSORBER  
 REDUCES NOISE

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM



**> MATERIAL:**  
 Silicone Gel

**> INSTALLATION:**




Divide for light load. Add for heavy load.  
 Make sure of total subject load and then  
 select optimum gel sheet.

Example:

For 0.3 kgf load, add a board for extra weight  
 or divide **A10Z62MSN02** to reduce projections.

For 10 kgf load, divide **A10Z62MSN15** into pieces.

For 80 kgf load, use two of **A10Z62MSN50** and  
 divide if needed.



- I
- R
- T
- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- A

## METRIC COMPONENT

Catalog Number	Optimum Load kgf/sheet	Resonance Point Hz	Resonance Magnification dB	Recommended Frequency Hz	Deflection mm	Color
<b>A10Z62MSN02</b>	0.5 to 2	27 to 21	6	from 38	1.4 to 3	Yellow
<b>A10Z62MSN05</b>	2 to 5	29 to 23	8	from 40	1.5 to 2.5	Green
<b>A10Z62MSN15</b>	5 to 15	26 to 18	13	from 37	1.1 to 2.2	Orange
<b>A10Z62MSN50</b>	15 to 50	22 to 15	20 to 18	from 30	0.7 to 2	Blue

LOW COMPRESSION SET  
 HIGH WEATHER RESISTANCE  
 HIGH CHEMICAL RESISTANCE  
 EFFECTIVE IN NARROW SPACE

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM



**> MATERIAL:**  
 Silicone Gel

**> OPERATING TEMPERATURE:**  
 -40°C to +100°C




Fig. 1





Fig. 2



**METRIC COMPONENT**

Catalog Number	W	L	t
<b>Fig. 1 Tape</b>			
A10Z62MGT1	10	1000	1
A10Z62MGT2	20		
A10Z62MGT3	10	1000	2
A10Z62MGT4	20		
A10Z62MGT5	10	1000	3
A10Z62MGT6	20		
<b>Fig. 2 Chips*</b>			
A10Z62MGC1	10	10	3
A10Z62MGC2			5
A10Z62MGC3	15	15	3
A10Z62MGC4			5
A10Z62MGC5			10
A10Z62MGC6	20	20	3
A10Z62MGC7			5
A10Z62MGC8			10

\*Priced per sheet (25 chips per sheet)

