

The Synchromesh Drive System represents an entirely new approach to synchronous drives. At the heart of the system is a drive cable, which replaces conventional timing belts as well as other means of transmitting synchronous motion. The cable consists of a core bundle of stranded stainless steel wires encapsulated in a nylon jacket. Wound spirally around the nylon jacket is another cable of similar construction. The spiral member is bonded to the core cable to provide functional stability under load. The pitch of the spiral winding is carefully controlled during the winding and bonding processes.




The use of stranded wire and nylon resin produces an extremely flexible cable that opens up new design possibilities, which were previously not possible with any other synchronous drives. The schematic diagram shown below illustrates the geometric features of the x-y plotter. Synchromesh cables are capable of changing operating planes, limited only by the size and proximity of adjacent pulleys. This unique characteristic makes it possible to produce this plotter design without employing expensive lead screw drive components. This is only one example of the countless possibilities offered with Synchromesh Drive Systems.

Complementing the Synchromesh cables are the drive pulleys which have helical grooves on their outside diameter to accurately engage the spiral convolutions on the drive cable. An additional radial groove of half round cross section supports the core cable and provides lateral stability. Synchromesh cables can be readily secured to other mechanism members in many different ways as well as those offered in the catalog pages.

Please note, however, that the Synchromesh Drive Systems are intended for reciprocating motion applications and cannot be made endless.

> ADVANTAGES AND DESIGN FEATURES:

- Synchronous motion
- Flexible in all directions
- Miniature in size
- High strength
- Small bending radius
- Lightweight
- Low inertia
- Low tension required
- Chemically resistant
- Electrically conductive & insulated
- Pulleys available machined or molded
- Easy to mount attachments & end fittings
- Cables available up to 200 feet long



I
R
T
1
2
3
4
5
6
7
8
9
10
11
12
13
14
15
A

SYNCHROMESH DRIVE SELECTION TABLE

SDP/SI

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

Catalog Number		IDLER PULLEY STYLES			
CABLE	PULLEY	Steel / Ball Bearing	All Plastic	Plastic / Sintered Brg.	Nylon / Ball Bearing
A 6J 9MAS0605 or A 6J 9-AS0605	A 6P 9M060... or A 6P 9-060...	A 6C 9-00804 (.441)	A 6M 9-00804 (.493) A 6M 9-01004 (.611) A 6M 9-01204 (.709) A 6M 9-01606 (.861)	A 6T 9-00604 (.401) A 6T 9-00804 (.517) A 6T 9-01004 (.626) A 6T 9-01204 (.711)	A 6Z 9-01004 (.623) A 6Z9-01204 (.706) A 6Z 9-01604 (.906)
A 6J 9MAS0805 or A 6J 9-AS0805	A 6P 9M080... or A 6P 9-080...	A 6C 9-00804 (.489)	A 6M 9-01204 (.759) A 6M 9-01606 (1.009) A 6M 9-02006 (1.229)	A 6T 9-00804 (.544) A 6T 9-01204 (.769) A 6T 9-01706 (1.019) A 6T 9-02006 (1.179) A 6T 9-02008 (1.179)	A 6Z 9-01204 (.767) A 6Z 9-01604 (.992) A 6Z 9-02006 (1.199) A 6Z 9-01706 (1.029) A 6Z 9-02008 (1.199)
A 6J 9MAS1005 or A 6J 9-AS1005	A 6P 9M100... or A 6P 9-100...	—	A 6M 9-02408 (1.348)	A 6T 9-01706 (1.058) A 6T 9-02006 (1.253) A 6T 9-02008 (1.253) A 6T 9-02408 (1.348) A 6T 9-02412 (1.348)	A 6Z 9-02006 (1.258) A 6Z 9-01706 (1.064) A 6Z 9-02008 (1.258) A 6Z 9-02408 (1.388) A 6Z 9-02412 (1.388)
A 6J 9MAS1209 or A 6J 9-AS1209	A 6P 9M120... or A 6P 9-120...	A 6C 9-01606 (.866) A 6C 9-01706 (1.000)	A 6M 9-02408 (1.426) A 6M 9-02808 (1.476)	A 6T 9-02408 (1.421) A 6T 9-02808 (1.491) A 6T 9-02412 (1.421) A 6T 9-02812 (1.491)	A 6Z 9-02408 (1.476) A 6Z 9-02808 (1.501) A 6Z 9-02412 (1.476) A 6Z 9-02812 (1.501)

NOTE: Numbers shown in parentheses indicate pitch diameters of cable when wrapped around related pulley.
Example: Cable **A 6J 9MAS1005** when used with pulley A 6M 9-02408 has a pitch diameter of 1.348.

METRIC SIZE BORES ARE AVAILABLE ON REQUEST.

PATENTED
MINIATURE
SYNCHRONOUS

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM



> MATERIAL:

- Cable Core - Stainless Steel 304
- Cable Casing - Nylon

> SPECIFICATIONS:

Life Data:


- 10⁶ minimum flexing cycles where:
- Pulley Pitch Radius (R) = 2 x P

Accuracy:

- Pitch Error ± 0.05 mm
- Cumulative Pitch Error ± 4.07 mm max. over 100 pitches.

Ambient Factors:

- Temperature Range: -30°C to +80°C
- Avoid strong acids, alkalies and organic solvents.




METRIC COMPONENT

Catalog Number	P Pitch	D Outside Dia. mm	D ₁ Dia.	W	Breaking Load N
Priced Per Meter					
A 6J 9MAS0605	3.048	1.6	0.6	0.6	160
A 6J 9MAS0805	3.81	2.2	0.8	0.8	323.4
A 6J 9MAS1005	5.08	2.8	1	1	529.2
A 6J 9MAS1209	6.35	3.4	1.2	1.2	784.5

PLUGS - Annealed Brass

METRIC COMPONENT

Catalog Number
Priced per 10 pieces
A 6J 9MB103




EYES - Steel, Nickel Plated

NOTE: Universal eyes fit all cable sizes and provide for convenient screw mounting.

METRIC COMPONENT

Catalog Number
Priced per 10 pieces
A 6J 9MAA39



The projections shown are per ISO convention.

SYNCHROMESH CABLE PULLEYS

SDP/SI

> MATERIAL:


Pulley - Acetal
Insert - Brass

Aluminum inserts used on 6.35 pitch pulleys.

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM



0 10



METRIC COMPONENT

Catalog Number	Pitch	No. of Grooves	P.D.	d Bore +0.025 0	S Face Width	L Length	D Hub Dia.	I Hub Proj. Ref.	Helix Angle	Set Screw
A 6P 9M0601502	3.048	15	14.55	2	3.6	9.5	10.3	5.9	45°	M2
A 6P 9M0601503				3						M2
A 6P 9M0601504				4						M2.5
A 6P 9M0602003		20	19.4	3	3.6	9.5	13.9	5.9	45°	M2
A 6P 9M0602004				4						M2.5
A 6P 9M0602005	5			M3						
A 6P 9M0602503	25	24.26	3	3.6	9.5	13.9	5.9	45°	M2	
A 6P 9M0602504			4						M2.5	
A 6P 9M0602505			5						M3	
A 6P 9M0801503	3.81	15	18.19	3	3.6	9.5	13.9	5.9	51°	M2
A 6P 9M0801504				4						M2.5
A 6P 9M0801505				5						M3
A 6P 9M0802403		24	29.11	3	3.6	9.5	15.9	5.9	51°	M2
A 6P 9M0802404				4						M2.5
A 6P 9M0802405	5	M3								
A 6P 9M1001506	5.08	15	24.26	6	4.8	12.7	15.9	7.9	42°	M4
A 6P 9M1003008		30	48.51	8			17.1			M5
A 6P 9M1201510	6.35	15	30.3	10	6.4	15.9	22.2	9.5	48°	M5
A 6P 9M1203010		30	60.63							

LOOP SLEEVES
THIMBLES
CRIMPING TOOL


PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

> MATERIAL:

Loop Sleeves - Copper, Zinc Plated
Thimbles - Stainless Steel


P = Pin Diameter
K = Distance from bearing point to fitting

P should be at least five (5) times the cable diameter for guaranteed breaking strength and K should be at least 2.5 times P.



METRIC COMPONENT

Catalog Number	For Cable No.'s	L Length After Swaging
Priced Per 10 Pieces		
A 6B 9MS039	A 6J 9MAS0605	11.1
A 6B 9MS063	A 6J 9MAS0805	11.9
A 6B 9MS093	A 6J 9MAS1005	12.7
A 6B 9MS093	A 6J 9MAS1209	12.7




Thimbles provide loop support at higher loads & protect cables from wear when motion is present. Some thimbles may have open and/or uneven ends.



METRIC COMPONENT

Catalog Number	For Cable No.'s	A	B	C	D	E	F
Priced Per 10 Pieces							
A 6C 9MT015	A 6J 9MAS0605	4.77	6.35	3.18	3.18	0.38	1.17
A 6C 9MT047	A 6J 9MAS0805	8.61	17.06	4.75	2.38	0.81	1.98
A 6C 9MT047	A 6J 9MAS1005	8.61	17.06	4.75	2.38	0.81	1.98
A 6C 9MT094	A 6J 9MAS1209	8.61	17.86	5.54	3.57	0.81	1.98

This precision crimping tool gives compound leverage of at least 15-1. The scissor-action plier-type tool has jaws which are made of a tough chrome alloy steel. All component parts of the tool are hardened and tempered. The handles have nonslip plastic grips. Easy to use.



METRIC COMPONENT

Catalog Number	For Cable No.'s
A 6O 9M00	A 6J 9MAS0605 A 6J 9MAS0805
A 6O 9M01	A 6J 9MAS1005 A 6J 9MAS1209

- I
- R
- T
- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- A