





Specifications	
Precision grade	JIS B 1704: 1978 grade 2
Gear teeth	Gleason
Pressure angle	20°
Helix angle	35°
Material	S45C
Heat treatment	Teeth induction hardened
Tooth hardness	50 ~ 60HRC
Surface treatment	Black oxide coated except for ground part



Catalog No.	Gear ratio	Module	No. of teeth	Direction of spiral	Shape	Bore		Pitch dia.	Outside dia.	Mounting distance	Total length	Crown to back length
						A _{H7}	B					
KSBSG2-3020R KSBSG2-2030L	1.5	m2	30	R	B4	12	35	60	61.6	40	26.6	21.2
			20	L	B3	10	30	40	43.55	45	24.91	16.18
		m2.5	30	R	B4	15	45	75	77.09	50	33.86	26.56
			20	L	B3	12	40	50	54.43	55	30.88	18.98
		m3	30	R	B4	16	50	90	92.21	55	35.34	26.66
			20	L	B3	16	45	60	65.58	70	40.17	26.86
m4	30	R	B4	20	70	120	122.85	75	47.49	37.14		
	20	L	B3	20	60	80	87.34	90	48.17	32.45		
KSBSG2-4020R KSBSG2-2040L	2	m2	40	R	B4	12	40	80	80.99	45	32.26	25.99
			20	L	B3	12	32	40	44.10	60	34.04	21.02
		m2.5	40	R	B4	15	50	100	101.27	55	39.65	31.27
			20	L	B3	12	40	50	55.21	75	43.61	26.30
		m3	40	R	B4	20	60	120	121.48	65	45.76	36.48
			20	L	B3	16	50	60	66.06	90	50.63	31.52
m4	40	R	B4	20	70	160	162.07	80	53.69	42.07		
	20	L	B3	20	60	80	88.50	120	66.24	42.12		
KSBSG2-4515R KSBSG2-1545L	3	m2	45	R	B4	12	40	90	90.67	40	30.29	26.01
			15	L	B3	10	24	30	34.78	60	29.66	15.80
		m2.5	45	R	B4	15	50	112.5	113.32	50	38.25	32.47
			15	L	B3	12	30	37.5	43.36	75	38.27	19.73
		m3	45	R	B4	20	60	135	135.99	55	40.59	33.98
			15	L	B3	15	38	45	52.08	90	44.98	23.68


Hub width	Length of bore	Face width	Holding surface dia.	Allowable torque (N-m)		Allowable torque (kgf-m)		Backlash (mm)	Weight (kg)	Catalog No.
				Bending strength	Surface durability	Bending strength	Surface durability			
15	23	11	37.56	14.1	14.2	1.44	1.44	0.05~0.11	0.26	KSBSG2-3020R KSBSG2-2030L
11.67	22	11	21.34	9.61	9.44	0.98	0.96			
18	30	15	45.61	29.0	29.7	2.96	3.03	0.06~0.12	0.55	KSBSG2.5-3020R KSBSG2.5-2030L
14.17	28	15	27.42	19.8	19.8	2.02	2.02			
17	31	17	57.14	48.4	50.4	4.94	5.14	0.07~0.13	0.82	KSBSG3-3020R KSBSG3-2030L
20	37	17	34.71	33.1	33.6	3.37	3.42			
25	40	20	78.59	106	113	10.8	11.5	0.10~0.16	1.90	KSBSG4-3020R KSBSG4-2030L
23.33	43	20	46.89	72.2	75.3	7.36	7.68			
18	27	15	48.46	25.5	26.7	2.60	2.73	0.05~0.11	0.51	KSBSG2-4020R KSBSG2-2040L
18	32	15	20.92	12.8	13.4	1.30	1.36			
20	34	20	59.28	51.7	55.1	5.27	5.62	0.06~0.12	1.06	KSBSG2.5-4020R KSBSG2.5-2040L
22.5	40	20	20.56	25.9	27.6	2.64	2.81			
24	38	22	73.81	84.8	91.9	8.65	9.38	0.07~0.13	1.67	KSBSG3-4020R KSBSG3-2040L
27.5	47	22	29.61	42.5	46.0	4.33	4.69			
28	45	28	102.39	195	217	19.9	22.2	0.10~0.16	3.33	KSBSG4-4020R KSBSG4-2040L
35	62	28	42.78	97.9	109	9.98	11.1			
17	26	15	59.04	34.8	28.1	3.55	2.87	0.05~0.11	0.60	KSBSG2-4515R KSBSG2-1545L
14	29	15	19.13	11.2	9.38	1.14	0.96			
22	35	20	72.84	59.0	48.3	6.01	4.93	0.06~0.12	1.21	KSBSG2.5-4515R KSBSG2.5-1545L
17.5	37	20	20.51	18.9	16.1	1.93	1.64			
20	35	23	88.18	99.3	82.5	10.1	8.41	0.07~0.13	1.99	KSBSG3-4515R KSBSG3-1545L
21.33	44	23	28.54	31.8	27.5	3.24	2.80			

- [Caution on Product Characteristics]
- Allowable torques shown in the table are the calculated values according to the assumed usage conditions. Please see page 303 for more details.
 - Dimensions of the outside diameter, the overall length and crown to back length are all theoretical values, and some differences will occur due to the corner chamfering of the gear tips.
 - These gears produce axial thrust forces. Please see Page 304 for more details.

- [Caution on Secondary Operations]
- Please read "Caution on Performing Secondary Operations" (Page 304) when performing modifications and/or secondary operations for safety concerns.
 - Due to the gear teeth being induction hardened, no secondary operations can be performed on tooth areas including the bottom land (approx. 2 to 3 mm).

Contact Surface of Spiral Bevel Gears

Tooth surfaces of spiral gears have concave and convex sides. Changes in the rotational direction of the driving gear alter the contact surface accordingly. The illustrations show the top view of RH and LH Spiral Gears, and the tables on the right explain the different contact surface depending on the situation.



RH Spiral as a driving gear

Rotating Direction of Driving Gear <small>Note 1</small>	Contact Surface	
	Driving Gear (RH Spiral)	Driving Gear (LH Spiral)
RH Rotation (Clockwise)	Convex Surface	Concave Surface
LH rotation (counterclockwise)	Concave Surface	Convex Surface

LH Spiral as a driving gear

Rotating Direction of Driving Gear <small>Note 1</small>	Contact Surface	
	Driving Gear (LH Spiral)	Driving Gear (RH Spiral)
RH Rotation (Clockwise)	Concave Surface	Convex Surface
LH Rotation (Counterclockwise)	Convex Surface	Concave Surface

(Note 1) Rotation directions given in the tables are for viewing the gears from the hub side.

Forces Acting on Spiral Bevel Gear Teeth

For a spiral bevel gear with shaft angle $\Sigma=90^\circ$, pressure angle $\alpha_n=20^\circ$, and spiral angle $\beta_m=35^\circ$, the tables below show the axial thrust force F_x and the radial force F_r when a tangential force F_t of 100 units is applied at the center of face width. For details, please refer to separate technical reference book, section of "Features of Tooth Surface Contact" (Page 107).

The tables show the values of $\frac{\text{Axial Thrust Force } F_x}{\text{Radial Force } F_r}$

(1) Forces acting upon pinion

Contact Surface	Gear Ratio z_2/z_1						
	1.0	1.5	2.0	2.5	3.0	4.0	5.0
Concave Surface	80.9	82.9	82.5	81.5	80.5	78.7	77.4
	-18.1	-1.9	8.4	15.2	20.0	26.1	29.8
Convex Surface	-18.1	-33.6	-42.8	-48.5	-52.4	-57.2	-59.9
	80.9	75.8	71.1	67.3	64.3	60.1	57.3

(2) Forces acting upon gear

Contact Surface	Gear Ratio z_2/z_1						
	1.0	1.5	2.0	2.5	3.0	4.0	5.0
Concave Surface	80.9	75.8	71.1	67.3	64.3	60.1	57.3
	-18.1	-33.6	-42.8	-48.5	-52.4	-57.2	-59.9
Convex Surface	-18.1	-1.9	8.4	15.2	20.0	26.1	29.8
	80.9	82.9	82.5	81.5	80.5	78.7	77.4